

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246341

Luminaire Tested: P3AS05R709024DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246341
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709024DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 317.0 lumens
Efficiency: N/A
Efficacy: 44.0 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246341

CATALOG NUMBER: P3AS05R709024DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246341

CATALOG NUMBER: P3AS05R709024DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77		
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61		
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49		
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74358
5°	72991
10°	68825
15°	62475
20°	54628
25°	46091
30°	37727
35°	29286
40°	20954
45°	13273
50°	6618
55°	4052
60°	3465
65°	3217
70°	2821
75°	2626
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 13273 cd/sqm

TEST NUMBER: P1246341

CATALOG NUMBER: P3AS05R709024DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.9	9.8
10°-20°	76.6	24.2
20°-30°	87.2	27.5
30°-40°	68.2	21.5
40°-50°	33.5	10.6
50°-60°	10.3	3.3
60°-70°	6.1	1.9
70°-80°	3.2	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	194.7	61.4
0°-40°	262.9	82.9
0°-60°	306.7	96.7
0°-90°	317.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	317.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	339	
5°	332	31
15°	275	77
25°	190	87
35°	109	68
45°	43	34
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1246341

CATALOG NUMBER: P3AS05R709024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	339.1
2.5°	337.3
5°	331.6
7.5°	322.3
10°	309.1
12.5°	293.7
15°	275.2
17.5°	255.3
20°	234.1
22.5°	212.1
25°	190.5
27.5°	169.3
30°	149.0
32.5°	128.8
35°	109.4
37.5°	90.8
40°	73.2
42.5°	56.9
45°	42.8
47.5°	30.0
50°	19.4
52.5°	12.8
55°	10.6
57.5°	9.3
60°	7.9
62.5°	7.1
65°	6.2
67.5°	5.3
70°	4.4
72.5°	3.5
75°	3.1
77.5°	2.6
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)