

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247701

Luminaire Tested: P3AS20R459024D010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247701
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459024D010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 2400K CCT AND, 90CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1075.1 lumens
Efficiency: N/A
Efficacy: 37.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247701
CATALOG NUMBER: P3AS20R459024D010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1247701
 CATALOG NUMBER: P3AS20R459024D010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74			
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69			
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64			
7	83	73	67	63	81	72	67	62	71	66	62	70	65	62	69	65	61	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	320194
5°	312898
10°	288639
15°	250989
20°	206191
25°	160437
30°	118474
35°	83359
40°	52040
45°	28189
50°	15249
55°	13113
60°	11753
65°	10066
70°	8591
75°	8811
80°	7577
85°	7548

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 28189 cd/sqm



TEST NUMBER: P1247701
 CATALOG NUMBER: P3AS20R459024D010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.6	12.2
10°-20°	305.6	28.4
20°-30°	303.4	28.2
30°-40°	195.4	18.2
40°-50°	75.3	7.0
50°-60°	30.6	2.8
60°-70°	19.3	1.8
70°-80°	10.4	1.0
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	740.7	68.9
0°-40°	936.1	87.1
0°-60°	1042.0	96.9
0°-90°	1075.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1075.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1460	
5°	1422	132
15°	1106	306
25°	663	303
35°	311	195
45°	91	75
55°	34	31
65°	19	19
75°	10	10
85°	3	3
90°	0	



TEST NUMBER: P1247701
CATALOG NUMBER: P3AS20R459024D010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1460.2
2.5°	1452.8
5°	1421.5
7.5°	1367.8
10°	1296.3
12.5°	1206.9
15°	1105.6
17.5°	995.3
20°	883.6
22.5°	770.3
25°	663.1
27.5°	561.7
30°	467.9
32.5°	385.9
35°	311.4
37.5°	244.4
40°	181.8
42.5°	131.1
45°	90.9
47.5°	61.1
50°	44.7
52.5°	37.3
55°	34.3
57.5°	29.8
60°	26.8
62.5°	22.4
65°	19.4
67.5°	16.4
70°	13.4
72.5°	11.9
75°	10.4
77.5°	7.5
80°	6.0
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

(END OF REPORT)