

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247790

Luminaire Tested: P3AS20R609024D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247790
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609024D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 602.0 lumens
Efficiency: N/A
Efficacy: 20.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247790
CATALOG NUMBER: P3AS20R609024D010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1247790
 CATALOG NUMBER: P3AS20R609024D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91				91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82				82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61				61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56				56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51				51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47				47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44				44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41				41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106855
5°	105657
10°	102002
15°	96368
20°	88838
25°	80424
30°	71403
35°	61034
40°	48519
45°	34205
50°	20434
55°	10322
60°	9911
65°	9080
70°	8463
75°	8049
80°	7324
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34205 cd/sqm



TEST NUMBER: P1247790
 CATALOG NUMBER: P3AS20R609024D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.1	7.5
10°-20°	118.6	19.7
20°-30°	152.3	25.3
30°-40°	141.2	23.5
40°-50°	86.0	14.3
50°-60°	28.6	4.8
60°-70°	17.4	2.9
70°-80°	9.8	1.6
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	316.1	52.5
0°-40°	457.3	76.0
0°-60°	571.9	95.0
0°-90°	602.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	602.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	487	
5°	480	45
15°	424	119
25°	332	152
35°	228	141
45°	110	86
55°	27	29
65°	18	17
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P1247790
CATALOG NUMBER: P3AS20R609024D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	487.3
2.5°	485.1
5°	480.0
7.5°	470.5
10°	458.1
12.5°	442.8
15°	424.5
17.5°	403.3
20°	380.7
22.5°	356.6
25°	332.4
27.5°	307.6
30°	282.0
32.5°	256.5
35°	228.0
37.5°	198.0
40°	169.5
42.5°	139.6
45°	110.3
47.5°	85.5
50°	59.9
52.5°	35.8
55°	27.0
57.5°	24.8
60°	22.6
62.5°	19.7
65°	17.5
67.5°	15.3
70°	13.2
72.5°	11.0
75°	9.5
77.5°	7.3
80°	5.8
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

(END OF REPORT)