

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246463

Luminaire Tested: P3AS09R259024DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259024DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 414.0 lumens
Efficiency: N/A
Efficacy: 37.3 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246463

CATALOG NUMBER: P3AS09R259024DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246463

CATALOG NUMBER: P3AS09R259024DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150295
5°	144199
10°	126317
15°	101544
20°	78010
25°	59036
30°	42665
35°	28349
40°	17175
45°	10017
50°	6379
55°	5199
60°	4517
65°	3995
70°	3334
75°	3304
80°	2399
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 10017 cd/sqm

TEST NUMBER: P1246463

CATALOG NUMBER: P3AS09R259024DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.6	14.4
10°-20°	123.7	29.9
20°-30°	111.9	27.0
30°-40°	67.2	16.2
40°-50°	26.7	6.4
50°-60°	12.3	3.0
60°-70°	7.5	1.8
70°-80°	4.0	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	295.2	71.3
0°-40°	362.4	87.5
0°-60°	401.4	96.9
0°-90°	414.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	414.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	685	
5°	655	60
15°	447	124
25°	244	112
35°	106	67
45°	32	27
55°	14	12
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1246463

CATALOG NUMBER: P3AS09R259024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	685.4
1°	685.4
2°	682.2
3°	675.1
4°	666.1
5°	655.1
6°	640.9
7°	624.8
8°	606.1
9°	587.3
10°	567.3
11°	544.1
12°	520.2
13°	496.3
14°	472.5
15°	447.3
17.5°	387.9
20°	334.3
22.5°	285.9
25°	244.0
27.5°	204.6
30°	168.5
32.5°	135.5
35°	105.9
37.5°	80.7
40°	60.0
42.5°	43.9
45°	32.3
47.5°	24.5
50°	18.7
52.5°	15.5
55°	13.6
57.5°	11.6
60°	10.3
62.5°	8.4
65°	7.7
67.5°	6.5
70°	5.2
72.5°	4.5
75°	3.9
77.5°	3.2
80°	1.9
82.5°	1.3
85°	1.3
87.5°	0.6



TEST NUMBER: P1246463

CATALOG NUMBER: P3AS09R259024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)