

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246466

Luminaire Tested: P3AS09R259024DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259024DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 372.0 lumens
Efficiency: N/A
Efficacy: 33.5 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246466
CATALOG NUMBER: P3AS09R259024DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1246466
 CATALOG NUMBER: P3AS09R259024DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	124990
5°	118093
10°	100377
15°	79501
20°	60415
25°	45075
30°	32790
35°	23182
40°	15744
45°	10978
50°	9211
55°	8908
60°	9385
65°	9651
70°	9553
75°	10252
80°	11744
85°	11825

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 12600 cd/sqm



TEST NUMBER: P1246466
 CATALOG NUMBER: P3AS09R259024DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	13.0
10°-20°	96.9	26.1
20°-30°	85.8	23.1
30°-40°	54.7	14.7
40°-50°	28.9	7.8
50°-60°	21.3	5.7
60°-70°	18.1	4.9
70°-80°	12.8	3.4
80°-90°	5.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	231.2	62.1
0°-40°	285.9	76.8
0°-60°	336.1	90.3
0°-90°	372.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	372.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	570	
5°	536	48
15°	350	97
25°	186	86
35°	87	55
45°	35	29
55°	23	21
65°	19	18
75°	12	13
85°	5	5
90°	0	



TEST NUMBER: P1246466
CATALOG NUMBER: P3AS09R259024DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	570.0
2.5°	561.6
5°	536.5
7.5°	497.4
10°	450.8
12.5°	400.5
15°	350.2
17.5°	301.8
20°	258.9
22.5°	219.8
25°	186.3
27.5°	156.5
30°	129.5
32.5°	106.2
35°	86.6
37.5°	68.9
40°	55.0
42.5°	43.8
45°	35.4
47.5°	30.7
50°	27.0
52.5°	25.1
55°	23.3
57.5°	22.4
60°	21.4
62.5°	19.6
65°	18.6
67.5°	16.8
70°	14.9
72.5°	14.0
75°	12.1
77.5°	10.2
80°	9.3
82.5°	7.5
85°	4.7
87.5°	1.9
90°	0.0

(END OF REPORT)