

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246516

Luminaire Tested: P3AS09R359024DE010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1246516  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R359024DE010 E3DLD1WH  
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 522.0 lumens  
Efficiency: N/A  
Efficacy: 47.0 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246516  
CATALOG NUMBER: P3AS09R359024DE010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1246516  
 CATALOG NUMBER: P3AS09R359024DE010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69		
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59		
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55		
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51		
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48		
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	119245
5°	116707
10°	109305
15°	98116
20°	85337
25°	72730
30°	60921
35°	48533
40°	35094
45°	22204
50°	12110
55°	8372
60°	7938
65°	7368
70°	7052
75°	6015
80°	5683
85°	4780

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22204 cd/sqm



TEST NUMBER: P1246516  
 CATALOG NUMBER: P3AS09R359024DE010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.3	9.5
10°-20°	120.3	23.0
20°-30°	137.8	26.4
30°-40°	112.5	21.5
40°-50°	56.7	10.9
50°-60°	21.1	4.0
60°-70°	14.1	2.7
70°-80°	7.8	1.5
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	307.4	58.9
0°-40°	419.9	80.4
0°-60°	497.7	95.3
0°-90°	522.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	522.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	544	
5°	530	49
15°	432	120
25°	301	138
35°	181	112
45°	72	57
55°	22	21
65°	14	14
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P1246516  
CATALOG NUMBER: P3AS09R359024DE010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	543.8
1°	543.1
2°	541.8
3°	539.3
4°	535.4
5°	530.2
6°	523.8
7°	517.3
8°	508.9
9°	500.6
10°	490.9
11°	480.6
12°	469.6
13°	457.3
14°	444.4
15°	432.2
17.5°	399.3
20°	365.7
22.5°	331.6
25°	300.6
27.5°	270.3
30°	240.6
32.5°	210.9
35°	181.3
37.5°	151.6
40°	122.6
42.5°	95.5
45°	71.6
47.5°	51.6
50°	35.5
52.5°	25.8
55°	21.9
57.5°	20.0
60°	18.1
62.5°	16.1
65°	14.2
67.5°	12.3
70°	11.0
72.5°	9.0
75°	7.1
77.5°	5.8
80°	4.5
82.5°	3.2
85°	1.9
87.5°	1.3



TEST NUMBER: P1246516  
CATALOG NUMBER: P3AS09R359024DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)