

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247817

Luminaire Tested: P3AS20R659024D010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247817
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659024D010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1033.0 lumens
Efficiency: N/A
Efficacy: 35.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247817
CATALOG NUMBER: P3AS20R659024D010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1247817
 CATALOG NUMBER: P3AS20R659024D010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62			
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	262567
5°	256042
10°	238428
15°	213690
20°	184536
25°	153517
30°	121057
35°	89704
40°	61830
45°	38330
50°	20844
55°	13113
60°	11096
65°	10066
70°	8591
75°	7540
80°	7577
85°	7548

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 38330 cd/sqm



TEST NUMBER: P1247817
 CATALOG NUMBER: P3AS20R659024D010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.1	10.5
10°-20°	261.6	25.3
20°-30°	289.3	28.0
30°-40°	210.1	20.3
40°-50°	98.4	9.5
50°-60°	33.2	3.2
60°-70°	19.1	1.9
70°-80°	10.0	1.0
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	658.9	63.8
0°-40°	869.0	84.1
0°-60°	1000.6	96.9
0°-90°	1033.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1033.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1197	
5°	1163	108
15°	941	262
25°	634	289
35°	335	210
45°	124	98
55°	34	33
65°	19	19
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P1247817
CATALOG NUMBER: P3AS20R659024D010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1197.4
2.5°	1190.0
5°	1163.2
7.5°	1123.0
10°	1070.8
12.5°	1009.8
15°	941.3
17.5°	866.8
20°	790.8
22.5°	711.9
25°	634.5
27.5°	555.5
30°	478.1
32.5°	403.6
35°	335.1
37.5°	272.5
40°	216.0
42.5°	165.3
45°	123.6
47.5°	89.4
50°	61.1
52.5°	41.7
55°	34.3
57.5°	29.8
60°	25.3
62.5°	22.3
65°	19.4
67.5°	16.4
70°	13.4
72.5°	11.9
75°	8.9
77.5°	7.4
80°	6.0
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

(END OF REPORT)