

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246518

Luminaire Tested: P3AS09R359024DE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1246518  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R359024DE010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 205.0 lumens  
Efficiency: N/A  
Efficacy: 18.5 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246518  
CATALOG NUMBER: P3AS09R359024DE010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1246518  
 CATALOG NUMBER: P3AS09R359024DE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	65894
5°	64275
10°	58761
15°	49875
20°	39483
25°	29857
30°	21750
35°	14696
40°	9046
45°	5179
50°	3138
55°	2523
60°	2237
65°	1972
70°	1603
75°	1610
80°	1642
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5179 cd/sqm



TEST NUMBER: P1246518  
 CATALOG NUMBER: P3AS09R359024DE010 E3DLP1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	27.0	13.2
10°-20°	60.6	29.5
20°-30°	56.7	27.6
30°-40°	34.7	16.9
40°-50°	13.7	6.7
50°-60°	6.0	2.9
60°-70°	3.8	1.8
70°-80°	2.0	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	144.2	70.3
0°-40°	178.9	87.3
0°-60°	198.6	96.9
0°-90°	205.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	205.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	300	
5°	292	27
15°	220	61
25°	123	57
35°	55	35
45°	17	14
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1246518  
CATALOG NUMBER: P3AS09R359024DE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	300.5
1°	300.8
2°	299.9
3°	298.0
4°	295.1
5°	292.0
6°	287.9
7°	283.1
8°	277.5
9°	271.1
10°	263.9
11°	256.3
12°	248.1
13°	239.3
14°	229.5
15°	219.7
17.5°	194.4
20°	169.2
22.5°	144.9
25°	123.4
27.5°	103.5
30°	85.9
32.5°	69.4
35°	54.9
37.5°	42.0
40°	31.6
42.5°	22.7
45°	16.7
47.5°	12.0
50°	9.2
52.5°	7.6
55°	6.6
57.5°	5.7
60°	5.1
62.5°	4.4
65°	3.8
67.5°	3.2
70°	2.5
72.5°	2.2
75°	1.9
77.5°	1.6
80°	1.3
82.5°	0.9
85°	0.6
87.5°	0.3



TEST NUMBER: P1246518  
CATALOG NUMBER: P3AS09R359024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)