

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246592

Luminaire Tested: P3AS09R509024DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246592
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509024DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 355.9 lumens
Efficiency: N/A
Efficacy: 32.1 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246592

CATALOG NUMBER: P3AS09R509024DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246592

CATALOG NUMBER: P3AS09R509024DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	97	92	88		101	95	91	87		93	89	86		90	87	84		88	85	83
4	98	91	85	81		96	90	85	81		87	83	80		85	82	79		84	81	78
5	93	85	80	76		92	84	79	75		83	78	74		81	77	74		79	76	73
6	89	80	75	71		88	80	74	70		78	73	70		77	73	69		75	72	69
7	85	76	70	66		84	75	70	66		74	69	66		73	69	65		72	68	65
8	81	72	66	62		80	71	66	62		70	65	62		69	65	62		68	64	61
9	78	68	63	59		76	68	62	59		67	62	59		66	62	58		65	61	58
10	74	65	59	56		73	65	59	56		64	59	55		63	59	55		62	58	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113346
5°	111050
10°	104028
15°	93122
20°	78360
25°	59810
30°	38867
35°	23048
40°	13311
45°	6667
50°	2490
55°	1950
60°	1798
65°	1660
70°	1603
75°	1610
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6667 cd/sqm

TEST NUMBER: P1246592

CATALOG NUMBER: P3AS09R509024DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.9	13.2
10°-20°	113.4	31.9
20°-30°	111.3	31.3
30°-40°	56.1	15.7
40°-50°	17.7	5.0
50°-60°	4.6	1.3
60°-70°	3.2	0.9
70°-80°	2.0	0.6
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	271.7	76.3
0°-40°	327.7	92.1
0°-60°	350.0	98.3
0°-90°	355.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	355.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	517	
5°	504	47
15°	410	113
25°	247	111
35°	86	56
45°	22	18
55°	5	5
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1246592

CATALOG NUMBER: P3AS09R509024DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	516.9
2.5°	513.7
5°	504.5
7.5°	488.1
10°	467.2
12.5°	440.3
15°	410.2
17.5°	375.4
20°	335.8
22.5°	293.1
25°	247.2
27.5°	198.5
30°	153.5
32.5°	115.5
35°	86.1
37.5°	63.6
40°	46.5
42.5°	32.9
45°	21.5
47.5°	12.3
50°	7.3
52.5°	5.4
55°	5.1
57.5°	4.4
60°	4.1
62.5°	3.8
65°	3.2
67.5°	2.8
70°	2.5
72.5°	2.2
75°	1.9
77.5°	1.6
80°	1.3
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)