

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247973

Luminaire Tested: P3AS02R159027DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247973
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159027DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 116.0 lumens
Efficiency: N/A
Efficacy: 32.2 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247973
CATALOG NUMBER: P3AS02R159027DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1247973

CATALOG NUMBER: P3AS02R159027DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	94	93	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	90	88	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	87	86	85	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	82	81	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	80	79	78	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	77	76	75	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	74	73	72	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	72	71	70	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	68	67	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	66	65	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99093
5°	87959
10°	61077
15°	36118
20°	20582
25°	11759
30°	6507
35°	3480
40°	1918
45°	1054
50°	648
55°	497
60°	439
65°	415
70°	385
75°	339
80°	253
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1054 cd/sqm



TEST NUMBER: P1247973

CATALOG NUMBER: P3AS02R159027DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.0	29.3
10°-20°	44.8	38.7
20°-30°	23.1	19.9
30°-40°	8.7	7.5
40°-50°	2.9	2.5
50°-60°	1.2	1.0
60°-70°	0.8	0.7
70°-80°	0.4	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	101.9	87.9
0°-40°	110.6	95.3
0°-60°	114.7	98.8
0°-90°	116.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	116.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	452	
5°	400	34
15°	159	45
25°	49	23
35°	13	9
45°	3	3
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1247973
CATALOG NUMBER: P3AS02R159027DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	451.9
1°	451.0
2°	445.1
3°	433.8
4°	418.9
5°	399.6
6°	377.7
7°	353.7
8°	327.0
9°	300.6
10°	274.3
12.5°	211.1
15°	159.1
17.5°	119.1
20°	88.2
22.5°	65.8
25°	48.6
27.5°	35.4
30°	25.7
32.5°	18.2
35°	13.0
37.5°	9.3
40°	6.7
42.5°	4.8
45°	3.4
47.5°	2.5
50°	1.9
52.5°	1.6
55°	1.3
57.5°	1.1
60°	1.0
62.5°	0.9
65°	0.8
67.5°	0.7
70°	0.6
72.5°	0.6
75°	0.4
77.5°	0.3
80°	0.2
82.5°	0.2
85°	0.1
87.5°	0.0
90°	0.0

(END OF REPORT)