

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246627

Luminaire Tested: P3AS09R559024DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246627
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559024DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 268.0 lumens
Efficiency: N/A
Efficacy: 24.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246627

CATALOG NUMBER: P3AS09R559024DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246627

CATALOG NUMBER: P3AS09R559024DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	96		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50391
5°	49747
10°	47784
15°	44699
20°	40767
25°	36389
30°	31828
35°	26448
40°	20839
45°	14141
50°	8631
55°	4473
60°	4166
65°	3943
70°	3654
75°	3219
80°	3157
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14141 cd/sqm

TEST NUMBER: P1246627

CATALOG NUMBER: P3AS09R559024DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.2	7.9
10°-20°	55.0	20.5
20°-30°	68.9	25.7
30°-40°	61.5	23.0
40°-50°	36.0	13.4
50°-60°	12.4	4.6
60°-70°	7.5	2.8
70°-80°	4.2	1.6
80°-90°	1.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	145.1	54.2
0°-40°	206.7	77.1
0°-60°	255.1	95.2
0°-90°	268.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	268.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	230	
5°	226	21
15°	197	55
25°	150	69
35°	99	62
45°	46	36
55°	12	12
65°	8	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1246627

CATALOG NUMBER: P3AS09R559024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	229.8
2.5°	228.5
5°	226.0
7.5°	220.9
10°	214.6
12.5°	206.7
15°	196.9
17.5°	186.4
20°	174.7
22.5°	162.7
25°	150.4
27.5°	138.0
30°	125.7
32.5°	112.4
35°	98.8
37.5°	85.5
40°	72.8
42.5°	59.2
45°	45.6
47.5°	34.8
50°	25.3
52.5°	16.5
55°	11.7
57.5°	10.4
60°	9.5
62.5°	8.5
65°	7.6
67.5°	6.6
70°	5.7
72.5°	4.7
75°	3.8
77.5°	3.2
80°	2.5
82.5°	1.6
85°	0.9
87.5°	0.6
90°	0.0

(END OF REPORT)