

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246632

Luminaire Tested: P3AS09R559024DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246632
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559024DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 546.0 lumens
Efficiency: N/A
Efficacy: 49.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246632
CATALOG NUMBER: P3AS09R559024DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1246632
 CATALOG NUMBER: P3AS09R559024DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	96	95	94	93	91				91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82				82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74				74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68				68
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62				62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57				57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52				52
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48				48
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45				45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42				42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102667
5°	101342
10°	97348
15°	91056
20°	83074
25°	74109
30°	64820
35°	53860
40°	42451
45°	28809
50°	17603
55°	9137
60°	8464
65°	8042
70°	7437
75°	6524
80°	6566
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 28809 cd/sqm



TEST NUMBER: P1246632

CATALOG NUMBER: P3AS09R559024DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.2	7.9
10°-20°	112.1	20.5
20°-30°	140.4	25.7
30°-40°	125.3	23.0
40°-50°	73.4	13.4
50°-60°	25.4	4.6
60°-70°	15.3	2.8
70°-80°	8.5	1.6
80°-90°	2.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	295.7	54.2
0°-40°	421.0	77.1
0°-60°	519.7	95.2
0°-90°	546.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	546.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	468	
5°	460	43
15°	401	112
25°	306	140
35°	201	125
45°	93	73
55°	24	25
65°	16	15
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1246632
CATALOG NUMBER: P3AS09R559024DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	468.2
2.5°	465.6
5°	460.4
7.5°	450.1
10°	437.2
12.5°	421.1
15°	401.1
17.5°	379.8
20°	356.0
22.5°	331.5
25°	306.3
27.5°	281.2
30°	256.0
32.5°	228.9
35°	201.2
37.5°	174.1
40°	148.3
42.5°	120.6
45°	92.9
47.5°	70.9
50°	51.6
52.5°	33.5
55°	23.9
57.5°	21.3
60°	19.3
62.5°	17.4
65°	15.5
67.5°	13.5
70°	11.6
72.5°	9.7
75°	7.7
77.5°	6.4
80°	5.2
82.5°	3.2
85°	1.9
87.5°	1.3
90°	0.0

(END OF REPORT)