

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247983

Luminaire Tested: P3AS02R159027DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247983
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159027DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 180.0 lumens
Efficiency: N/A
Efficacy: 50.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247983

CATALOG NUMBER: P3AS02R159027DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1247983

CATALOG NUMBER: P3AS02R159027DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	109	107	104		110	107	105	102		103	101	99		99	98	96		96	95	93
2	106	100	96	92		104	99	95	91		95	92	89		92	90	87		90	87	85
3	100	93	87	83		98	91	86	82		89	84	81		86	82	79		84	81	78
4	94	86	80	75		92	85	79	74		82	77	73		80	76	73		78	75	72
5	89	80	73	68		87	79	73	68		77	72	67		75	70	67		74	69	66
6	84	74	68	63		83	73	67	63		72	66	62		70	66	62		69	65	61
7	80	69	63	58		78	69	63	58		67	62	58		66	61	57		65	61	57
8	76	65	59	54		74	65	58	54		63	58	54		62	57	54		61	57	53
9	72	61	55	51		71	61	55	51		60	54	50		59	54	50		58	53	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45413
5°	44178
10°	40369
15°	35346
20°	30336
25°	25332
30°	20256
35°	15205
40°	11021
45°	7226
50°	4503
55°	3058
60°	2719
65°	2491
70°	2308
75°	2118
80°	2020
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7226 cd/sqm

TEST NUMBER: P1247983

CATALOG NUMBER: P3AS02R159027DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.5	10.3
10°-20°	43.4	24.1
20°-30°	47.8	26.6
30°-40°	35.8	19.9
40°-50°	18.6	10.3
50°-60°	7.7	4.3
60°-70°	4.8	2.7
70°-80°	2.7	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	109.7	60.9
0°-40°	145.5	80.8
0°-60°	171.8	95.4
0°-90°	180.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	180.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	207	
5°	201	19
15°	156	43
25°	105	48
35°	57	36
45°	23	19
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1247983

CATALOG NUMBER: P3AS02R159027DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	207.1
1°	207.3
2°	206.6
3°	205.2
4°	203.2
5°	200.7
6°	197.5
7°	194.1
8°	190.0
9°	185.6
10°	181.3
12.5°	168.7
15°	155.7
17.5°	142.7
20°	130.0
22.5°	117.0
25°	104.7
27.5°	92.4
30°	80.0
32.5°	68.0
35°	56.8
37.5°	47.2
40°	38.5
42.5°	30.6
45°	23.3
47.5°	17.6
50°	13.2
52.5°	9.8
55°	8.0
57.5°	7.1
60°	6.2
62.5°	5.5
65°	4.8
67.5°	4.1
70°	3.6
72.5°	3.0
75°	2.5
77.5°	2.1
80°	1.6
82.5°	1.1
85°	0.7
87.5°	0.2
90°	0.0

(END OF REPORT)