

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248015

Luminaire Tested: P3AS02R209027DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248015
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209027DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 179.0 lumens
Efficiency: N/A
Efficacy: 49.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248015

CATALOG NUMBER: P3AS02R209027DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1248015

CATALOG NUMBER: P3AS02R209027DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	109	106	104		110	107	105	102		103	101	99		99	98	96		96	95	93
2	106	100	96	92		104	99	94	91		95	92	89		92	89	87		90	87	85
3	100	93	87	82		98	91	86	82		88	84	80		86	82	79		84	81	78
4	94	86	79	75		92	85	79	74		82	77	73		80	76	72		78	75	72
5	89	80	73	68		87	79	73	68		77	71	67		75	70	67		73	69	66
6	84	74	68	63		82	73	67	63		72	66	62		70	65	62		69	65	61
7	80	69	63	58		78	69	62	58		67	62	58		66	61	57		65	60	57
8	75	65	59	54		74	64	58	54		63	58	54		62	57	53		61	57	53
9	72	61	55	50		70	61	55	50		60	54	50		59	54	50		58	53	50
10	68	58	51	47		67	57	51	47		56	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44273
5°	43099
10°	39634
15°	34892
20°	29916
25°	25139
30°	20332
35°	15473
40°	10992
45°	7257
50°	4503
55°	2944
60°	2675
65°	2491
70°	2308
75°	2118
80°	2020
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7257 cd/sqm

TEST NUMBER: P1248015

CATALOG NUMBER: P3AS02R209027DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.1	10.1
10°-20°	42.8	23.9
20°-30°	47.5	26.5
30°-40°	36.2	20.3
40°-50°	18.5	10.4
50°-60°	7.6	4.2
60°-70°	4.8	2.7
70°-80°	2.7	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	108.4	60.6
0°-40°	144.6	80.8
0°-60°	170.8	95.4
0°-90°	179.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	179.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	202	
5°	196	18
15°	154	43
25°	104	47
35°	58	36
45°	23	19
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1248015

CATALOG NUMBER: P3AS02R209027DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	201.9
1°	202.1
2°	201.2
3°	200.1
4°	198.3
5°	195.8
6°	192.8
7°	189.6
8°	186.2
9°	182.1
10°	178.0
12.5°	166.2
15°	153.7
17.5°	141.0
20°	128.2
22.5°	115.5
25°	103.9
27.5°	92.3
30°	80.3
32.5°	68.9
35°	57.8
37.5°	48.0
40°	38.4
42.5°	30.2
45°	23.4
47.5°	17.7
50°	13.2
52.5°	9.8
55°	7.7
57.5°	7.0
60°	6.1
62.5°	5.5
65°	4.8
67.5°	4.1
70°	3.6
72.5°	3.0
75°	2.5
77.5°	2.0
80°	1.6
82.5°	1.1
85°	0.7
87.5°	0.2
90°	0.0

(END OF REPORT)