

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246677

Luminaire Tested: P3AS09R659024DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1246677  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R659024DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 770.0 lumens  
Efficiency: N/A  
Efficacy: 69.4 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246677  
CATALOG NUMBER: P3AS09R659024DE010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1246677  
 CATALOG NUMBER: P3AS09R659024DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82	82	82	82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77	77	77	77
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67	67	67	67
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63	63	63	63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59	59	59	59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	206321
5°	191569
10°	185278
15°	178548
20°	165074
25°	150396
30°	116195
35°	67351
40°	26736
45°	11381
50°	2695
55°	344
60°	263
65°	156
70°	192
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11381 cd/sqm



TEST NUMBER: P1246677  
 CATALOG NUMBER: P3AS09R659024DE010 E3D1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.1	10.7
10°-20°	219.1	28.5
20°-30°	277.4	36.0
30°-40°	157.9	20.5
40°-50°	31.4	4.1
50°-60°	1.6	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	578.6	75.1
0°-40°	736.5	95.7
0°-60°	769.5	99.9
0°-90°	770.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	770.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	941	
5°	870	82
15°	786	219
25°	622	277
35°	252	158
45°	37	31
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1246677  
CATALOG NUMBER: P3AS09R659024DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	940.9
1°	934.0
2°	918.8
3°	901.0
4°	883.6
5°	870.3
6°	860.5
7°	852.6
8°	845.7
9°	838.7
10°	832.1
11°	824.8
12°	817.2
13°	808.0
14°	798.2
15°	786.5
16°	772.6
17°	757.4
18°	740.9
19°	723.5
20°	707.4
21°	690.9
22°	676.0
23°	660.5
24°	642.5
25°	621.6
26°	596.6
27°	566.5
28°	532.7
29°	496.6
30°	458.9
31°	417.4
32°	376.3
32.5°	355.1
33°	334.5
34°	292.8
35°	251.6
36°	213.6
37°	176.0
37.5°	156.7
38°	141.2
39°	114.3
40°	93.4
42.5°	57.6
45°	36.7



TEST NUMBER: P1246677  
CATALOG NUMBER: P3AS09R659024DE010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	21.5
50°	7.9
52.5°	1.6
55°	0.9
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)