

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246678

Luminaire Tested: P3AS09R659024DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246678
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659024DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 770.0 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246678

CATALOG NUMBER: P3AS09R659024DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246678

CATALOG NUMBER: P3AS09R659024DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	95	91	88	93	89	86		90	87	85		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	70	65	83	75	69	65	73	69	65		72	68	65		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		68
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	206321
5°	191569
10°	185278
15°	178548
20°	165074
25°	150396
30°	116195
35°	67351
40°	26736
45°	11381
50°	2695
55°	344
60°	263
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11381 cd/sqm

TEST NUMBER: P1246678

CATALOG NUMBER: P3AS09R659024DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.1	10.7
10°-20°	219.1	28.5
20°-30°	277.4	36.0
30°-40°	157.9	20.5
40°-50°	31.4	4.1
50°-60°	1.6	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	578.6	75.1
0°-40°	736.5	95.7
0°-60°	769.5	99.9
0°-90°	770.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	770.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	941	
5°	870	82
15°	786	219
25°	622	277
35°	252	158
45°	37	31
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1246678

CATALOG NUMBER: P3AS09R659024DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	940.9
1°	934.0
2°	918.8
3°	901.0
4°	883.6
5°	870.3
6°	860.5
7°	852.6
8°	845.7
9°	838.7
10°	832.1
11°	824.8
12°	817.2
13°	808.0
14°	798.2
15°	786.5
16°	772.6
17°	757.4
18°	740.9
19°	723.5
20°	707.4
21°	690.9
22°	676.0
23°	660.5
24°	642.5
25°	621.6
26°	596.6
27°	566.5
28°	532.7
29°	496.6
30°	458.9
31°	417.4
32°	376.3
32.5°	355.1
33°	334.5
34°	292.8
35°	251.6
36°	213.6
37°	176.0
37.5°	156.7
38°	141.2
39°	114.3
40°	93.4
42.5°	57.6
45°	36.7



TEST NUMBER: P1246678

CATALOG NUMBER: P3AS09R659024DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	21.5
50°	7.9
52.5°	1.6
55°	0.9
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)