

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248095

Luminaire Tested: P3AS02R359027DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359027DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 148.0 lumens
Efficiency: N/A
Efficacy: 41.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248095
CATALOG NUMBER: P3AS02R359027DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1248095
 CATALOG NUMBER: P3AS02R359027DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80	80	80	80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74	74	74	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69	69	69	69
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65	65	65	65
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61	61	61	61
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57	57	57	57
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54	54	54	54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47562
5°	46401
10°	42417
15°	36005
20°	28492
25°	21558
30°	15699
35°	10627
40°	6527
45°	3752
50°	2252
55°	1835
60°	1579
65°	1401
70°	1154
75°	1186
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3752 cd/sqm



TEST NUMBER: P1248095
 CATALOG NUMBER: P3AS02R359027DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.5	13.2
10°-20°	43.7	29.5
20°-30°	40.9	27.6
30°-40°	25.0	16.9
40°-50°	9.9	6.7
50°-60°	4.3	2.9
60°-70°	2.7	1.8
70°-80°	1.4	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	104.1	70.3
0°-40°	129.1	87.3
0°-60°	143.4	96.9
0°-90°	148.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	148.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	217	
5°	211	19
15°	159	44
25°	89	41
35°	40	25
45°	12	10
55°	5	4
65°	3	3
75°	1	1
85°	0	1
90°	0	



TEST NUMBER: P1248095
CATALOG NUMBER: P3AS02R359027DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	216.9
1°	217.2
2°	216.5
3°	215.1
4°	213.1
5°	210.8
6°	207.8
7°	204.4
8°	200.3
9°	195.7
10°	190.5
11°	185.0
12°	179.1
13°	172.7
14°	165.7
15°	158.6
17.5°	140.4
20°	122.1
22.5°	104.6
25°	89.1
27.5°	74.7
30°	62.0
32.5°	50.1
35°	39.7
37.5°	30.3
40°	22.8
42.5°	16.4
45°	12.1
47.5°	8.7
50°	6.6
52.5°	5.5
55°	4.8
57.5°	4.1
60°	3.6
62.5°	3.2
65°	2.7
67.5°	2.3
70°	1.8
72.5°	1.6
75°	1.4
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.5
87.5°	0.2



TEST NUMBER: P1248095
CATALOG NUMBER: P3AS02R359027DE010 E3DL1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)