

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246707

Luminaire Tested: P3AS09R709024DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246707
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709024DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 769.9 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246707

CATALOG NUMBER: P3AS09R709024DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246707

CATALOG NUMBER: P3AS09R709024DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86
4	95	87	81	77	94	86	81	77	84	79	76		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149725
5°	141184
10°	133865
15°	131465
20°	126711
25°	119450
30°	118601
35°	103276
40°	66811
45°	31569
50°	4435
55°	344
60°	263
65°	311
70°	192
75°	254
80°	379
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31569 cd/sqm

TEST NUMBER: P1246707

CATALOG NUMBER: P3AS09R709024DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.9	7.8
10°-20°	162.6	21.1
20°-30°	230.1	29.9
30°-40°	231.2	30.0
40°-50°	83.1	10.8
50°-60°	2.2	0.3
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	452.6	58.8
0°-40°	683.7	88.8
0°-60°	769.1	99.9
0°-90°	769.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	769.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	683	
5°	641	60
15°	579	163
25°	494	230
35°	386	231
45°	102	83
55°	1	2
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1246707

CATALOG NUMBER: P3AS09R709024DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	682.8
1°	680.9
2°	674.9
3°	665.4
4°	653.4
5°	641.4
6°	630.0
7°	621.1
8°	613.2
9°	606.9
10°	601.2
11°	596.4
12°	592.0
13°	587.6
14°	583.5
15°	579.1
16°	573.7
17°	568.0
18°	561.0
19°	552.5
20°	543.0
21°	532.6
22°	522.1
23°	512.0
24°	502.2
25°	493.7
26°	487.7
27°	482.9
28°	479.1
29°	474.7
30°	468.4
31°	459.2
32°	446.2
32.5°	439.0
33°	429.2
34°	409.9
35°	385.8
36°	359.3
37°	329.2
37.5°	315.3
38°	296.3
39°	262.5
40°	233.4
42.5°	161.6
45°	101.8

TEST NUMBER: P1246707

CATALOG NUMBER: P3AS09R709024DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	54.7
50°	13.0
52.5°	1.6
55°	0.9
57.5°	0.9
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)