

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248153

Luminaire Tested: P3AS02R459027DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459027DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 254.0 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248153

CATALOG NUMBER: P3AS02R459027DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1248153

CATALOG NUMBER: P3AS02R459027DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	86	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95387
5°	93154
10°	85636
15°	72554
20°	56285
25°	39341
30°	24789
35°	14589
40°	8244
45°	4000
50°	1399
55°	1147
60°	1096
65°	1038
70°	1026
75°	932
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4000 cd/sqm

TEST NUMBER: P1248153

CATALOG NUMBER: P3AS02R459027DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.2	15.4
10°-20°	87.8	34.6
20°-30°	74.5	29.3
30°-40°	35.5	14.0
40°-50°	10.7	4.2
50°-60°	2.7	1.1
60°-70°	2.0	0.8
70°-80°	1.2	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	201.5	79.3
0°-40°	237.0	93.3
0°-60°	250.4	98.6
0°-90°	254.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	254.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	435	
5°	423	39
15°	320	88
25°	163	75
35°	54	36
45°	13	11
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1248153

CATALOG NUMBER: P3AS02R459027DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	435.0
2.5°	432.3
5°	423.2
7.5°	407.5
10°	384.6
12.5°	354.1
15°	319.6
17.5°	281.2
20°	241.2
22.5°	200.6
25°	162.6
27.5°	128.1
30°	97.9
32.5°	73.6
35°	54.5
37.5°	40.2
40°	28.8
42.5°	20.0
45°	12.9
47.5°	7.3
50°	4.1
52.5°	3.2
55°	3.0
57.5°	2.7
60°	2.5
62.5°	2.3
65°	2.0
67.5°	1.8
70°	1.6
72.5°	1.4
75°	1.1
77.5°	0.9
80°	0.7
82.5°	0.5
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)