

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246714

Luminaire Tested: P3AS09R709024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 227.0 lumens
Efficiency: N/A
Efficacy: 20.4 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246714

CATALOG NUMBER: P3AS09R709024DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246714

CATALOG NUMBER: P3AS09R709024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53241
5°	52278
10°	49275
15°	44722
20°	39133
25°	33002
30°	27017
35°	20960
40°	15000
45°	9489
50°	4742
55°	2906
60°	2500
65°	2283
70°	2052
75°	1864
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9489 cd/sqm

TEST NUMBER: P1246714

CATALOG NUMBER: P3AS09R709024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.2	9.8
10°-20°	54.8	24.2
20°-30°	62.4	27.5
30°-40°	48.8	21.5
40°-50°	24.0	10.6
50°-60°	7.4	3.3
60°-70°	4.4	1.9
70°-80°	2.3	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	139.4	61.4
0°-40°	188.2	82.9
0°-60°	219.6	96.7
0°-90°	227.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	227.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	243	
5°	238	22
15°	197	55
25°	136	62
35°	78	49
45°	31	24
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1246714

CATALOG NUMBER: P3AS09R709024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	242.8
2.5°	241.6
5°	237.5
7.5°	230.8
10°	221.3
12.5°	210.3
15°	197.0
17.5°	182.8
20°	167.7
22.5°	151.9
25°	136.4
27.5°	121.3
30°	106.7
32.5°	92.2
35°	78.3
37.5°	65.0
40°	52.4
42.5°	40.7
45°	30.6
47.5°	21.5
50°	13.9
52.5°	9.2
55°	7.6
57.5°	6.6
60°	5.7
62.5°	5.1
65°	4.4
67.5°	3.8
70°	3.2
72.5°	2.5
75°	2.2
77.5°	1.9
80°	1.3
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)