

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248189

Luminaire Tested: P3AS02R509027DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248189
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509027DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 82.0 lumens
Efficiency: N/A
Efficacy: 22.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248189

CATALOG NUMBER: P3AS02R509027DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1248189

CATALOG NUMBER: P3AS02R509027DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23858
5°	23200
10°	21398
15°	18820
20°	15751
25°	12485
30°	9166
35°	6291
40°	4008
45°	2233
50°	1228
55°	1032
60°	877
65°	830
70°	705
75°	678
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2233 cd/sqm

TEST NUMBER: P1248189

CATALOG NUMBER: P3AS02R509027DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.8	11.9
10°-20°	23.0	28.0
20°-30°	23.5	28.6
30°-40°	14.9	18.1
40°-50°	5.9	7.2
50°-60°	2.4	2.9
60°-70°	1.5	1.9
70°-80°	0.8	1.0
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	56.2	68.6
0°-40°	71.1	86.7
0°-60°	79.4	96.9
0°-90°	82.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	82.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	109	
5°	105	10
15°	83	23
25°	52	23
35°	24	15
45°	7	6
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1248189

CATALOG NUMBER: P3AS02R509027DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	108.8
2.5°	108.0
5°	105.4
7.5°	101.4
10°	96.1
12.5°	89.8
15°	82.9
17.5°	75.4
20°	67.5
22.5°	59.6
25°	51.6
27.5°	43.6
30°	36.2
32.5°	29.5
35°	23.5
37.5°	18.4
40°	14.0
42.5°	10.3
45°	7.2
47.5°	4.9
50°	3.6
52.5°	3.0
55°	2.7
57.5°	2.3
60°	2.0
62.5°	1.8
65°	1.6
67.5°	1.3
70°	1.1
72.5°	0.9
75°	0.8
77.5°	0.6
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)