

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248230

Luminaire Tested: P3AS02R609027DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248230
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609027DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 273.0 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248230

CATALOG NUMBER: P3AS02R609027DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1248230

CATALOG NUMBER: P3AS02R609027DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	102		101	100	99		98	97	96
2	108	104	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	96	91	88		93	89	86		91	87	85		88	86	84
4	98	91	85	81		96	90	85	81		88	83	80		86	82	79		84	81	78
5	93	85	80	75		92	84	79	75		83	78	74		81	77	74		79	76	73
6	89	80	74	70		87	79	74	70		78	73	70		77	72	69		75	72	69
7	85	76	70	66		83	75	69	65		74	69	65		72	68	65		71	67	64
8	81	71	65	61		79	71	65	61		70	65	61		69	64	61		68	64	61
9	77	67	62	58		76	67	61	58		66	61	57		65	61	57		64	60	57
10	73	64	58	54		72	63	58	54		63	58	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71529
5°	67532
10°	65775
15°	64268
20°	59762
25°	53422
30°	40791
35°	23557
40°	9131
45°	3814
50°	853
55°	115
60°	88
65°	52
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3814 cd/sqm

TEST NUMBER: P1248230

CATALOG NUMBER: P3AS02R609027DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.0	10.6
10°-20°	78.9	28.9
20°-30°	98.8	36.2
30°-40°	55.2	20.2
40°-50°	10.5	3.8
50°-60°	0.5	0.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	206.6	75.7
0°-40°	261.8	95.9
0°-60°	272.8	99.9
0°-90°	273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	273.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	326	
5°	307	29
15°	283	79
25°	221	99
35°	88	55
45°	12	10
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1248230

CATALOG NUMBER: P3AS02R609027DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	326.2
1°	324.9
2°	320.6
3°	315.6
4°	310.9
5°	306.8
6°	303.6
7°	301.0
8°	299.0
9°	297.1
10°	295.4
11°	293.7
12°	291.8
13°	289.5
14°	286.7
15°	283.1
16°	278.7
17°	273.8
18°	268.2
19°	261.9
20°	256.1
21°	249.8
22°	243.3
23°	236.5
24°	229.0
25°	220.8
26°	211.1
27°	200.2
28°	188.1
29°	175.1
30°	161.1
31°	147.1
32°	132.6
32.5°	124.6
33°	117.5
34°	102.6
35°	88.0
36°	74.8
37°	60.9
37.5°	54.5
38°	48.2
39°	38.9
40°	31.9
42.5°	19.4
45°	12.3



TEST NUMBER: P1248230

CATALOG NUMBER: P3AS02R609027DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.8
50°	2.5
52.5°	0.6
55°	0.3
57.5°	0.2
60°	0.2
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)