

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246799

Luminaire Tested: P3AS13R159024DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1246799  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R159024DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R15 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 436.0 lumens  
Efficiency: N/A  
Efficacy: 29.9 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246799  
CATALOG NUMBER: P3AS13R159024DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1246799

CATALOG NUMBER: P3AS13R159024DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	93	93	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	88	88	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	85	85	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	81	81	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	78	78	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	75	75	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	73	73	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	70	70	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	68	68	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	372448
5°	330618
10°	229588
15°	135778
20°	77333
25°	44204
30°	24459
35°	13037
40°	7214
45°	3907
50°	2422
55°	1912
60°	1667
65°	1505
70°	1346
75°	1440
80°	1010
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3907 cd/sqm



TEST NUMBER: P1246799  
 CATALOG NUMBER: P3AS13R159024DE010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.7	29.3
10°-20°	168.6	38.7
20°-30°	86.8	19.9
30°-40°	32.6	7.5
40°-50°	10.7	2.4
50°-60°	4.6	1.1
60°-70°	2.9	0.7
70°-80°	1.7	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	383.1	87.9
0°-40°	415.7	95.3
0°-60°	430.9	98.8
0°-90°	436.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	436.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1698	
5°	1502	128
15°	598	169
25°	183	87
35°	49	33
45°	13	11
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1246799  
CATALOG NUMBER: P3AS13R159024DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1698.5
1°	1695.2
2°	1672.9
3°	1630.5
4°	1574.6
5°	1502.0
6°	1419.7
7°	1329.4
8°	1229.0
9°	1129.8
10°	1031.1
12.5°	793.4
15°	598.1
17.5°	447.7
20°	331.4
22.5°	247.4
25°	182.7
27.5°	133.1
30°	96.6
32.5°	68.5
35°	48.7
37.5°	34.9
40°	25.2
42.5°	18.1
45°	12.6
47.5°	9.2
50°	7.1
52.5°	5.9
55°	5.0
57.5°	4.2
60°	3.8
62.5°	3.4
65°	2.9
67.5°	2.5
70°	2.1
72.5°	2.1
75°	1.7
77.5°	1.3
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)