

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248264

Luminaire Tested: P3AS02R659027DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659027DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 112.0 lumens
Efficiency: N/A
Efficacy: 31.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248264

CATALOG NUMBER: P3AS02R659027DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1248264

CATALOG NUMBER: P3AS02R659027DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86	83	80	79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69	68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72	67	64	63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64	59	56	55
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60	56	53	51
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57	53	49	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26423
5°	26106
10°	25094
15°	23519
20°	21142
25°	17953
30°	14053
35°	10012
40°	6555
45°	4062
50°	2047
55°	726
60°	658
65°	623
70°	577
75°	593
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4062 cd/sqm

TEST NUMBER: P1248264

CATALOG NUMBER: P3AS02R659027DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.1	9.9
10°-20°	28.8	25.7
20°-30°	33.7	30.1
30°-40°	23.5	21.0
40°-50°	10.4	9.3
50°-60°	2.3	2.1
60°-70°	1.2	1.0
70°-80°	0.7	0.6
80°-90°	0.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	73.6	65.8
0°-40°	97.2	86.8
0°-60°	109.9	98.1
0°-90°	112.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	112.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	120	
5°	119	11
15°	104	29
25°	74	34
35°	37	24
45°	13	10
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1248264

CATALOG NUMBER: P3AS02R659027DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	120.5
2.5°	120.0
5°	118.6
7.5°	116.1
10°	112.7
12.5°	108.6
15°	103.6
17.5°	97.5
20°	90.6
22.5°	82.9
25°	74.2
27.5°	65.1
30°	55.5
32.5°	46.2
35°	37.4
37.5°	29.7
40°	22.9
42.5°	17.3
45°	13.1
47.5°	9.6
50°	6.0
52.5°	3.1
55°	1.9
57.5°	1.7
60°	1.5
62.5°	1.3
65°	1.2
67.5°	1.0
70°	0.9
72.5°	0.8
75°	0.7
77.5°	0.6
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)