

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246826

Luminaire Tested: P3AS13R209024DE010 E3D1B

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246826
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209024DE010 E3D1B
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3D1B TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1075.0 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246826

CATALOG NUMBER: P3AS13R209024DE010 E3D1B

Luminous Intensity Polar Plot



TEST NUMBER: P1246826

CATALOG NUMBER: P3AS13R209024DE010 E3D1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	114	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	101		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	95	99	96	94		97	95	93		95
5	104	98	95	92	102	98	94	92	96	93	91		95	92	90		93
6	101	96	92	89	100	95	92	89	94	91	89		93	90	88		92
7	99	93	90	87	98	93	89	87	92	89	86		91	88	86		90
8	97	91	87	85	96	91	87	85	90	87	85		89	86	84		88
9	95	89	85	83	94	89	85	83	88	85	83		87	84	83		87
10	93	87	84	81	92	87	83	81	86	83	81		86	83	81		85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1630681
5°	1372966
10°	857544
15°	320592
20°	110050
25°	45874
30°	21598
35°	9664
40°	4580
45°	2357
50°	853
55°	153
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2357 cd/sqm

TEST NUMBER: P1246826

CATALOG NUMBER: P3AS13R209024DE010 E3D1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	518.7	48.3
10°-20°	427.3	39.7
20°-30°	97.1	9.0
30°-40°	24.7	2.3
40°-50°	6.2	0.6
50°-60°	0.8	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1043.0	97.0
0°-40°	1067.7	99.3
0°-60°	1074.7	100.0
0°-90°	1075.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1075.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7436	
5°	6237	519
15°	1412	427
25°	190	97
35°	36	25
45°	8	6
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1246826

CATALOG NUMBER: P3AS13R209024DE010 E3D1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	7436.5
1°	7373.5
2°	7187.7
3°	6921.2
4°	6594.2
5°	6237.4
6°	5839.8
7°	5401.0
8°	4889.0
9°	4381.7
10°	3851.3
11°	3286.8
12°	2723.2
13°	2245.7
14°	1789.3
15°	1412.2
16°	1114.7
17°	879.3
18°	706.5
19°	574.6
20°	471.6
21°	394.3
22°	329.1
23°	273.6
24°	228.2
25°	189.6
27.5°	124.0
30°	85.3
32.5°	52.5
35°	36.1
37.5°	23.1
40°	16.0
42.5°	10.9
45°	7.6
47.5°	5.0
50°	2.5
52.5°	1.3
55°	0.4
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0

TEST NUMBER: P1246826

CATALOG NUMBER: P3AS13R209024DE010 E3D1B

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)