

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246831

Luminaire Tested: P3AS13R209024DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246831
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209024DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 435.0 lumens
Efficiency: N/A
Efficacy: 29.8 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246831

CATALOG NUMBER: P3AS13R209024DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246831

CATALOG NUMBER: P3AS13R209024DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78
9	85	78	73	70	85	77	73	70	77	73	70		76	72	69		75
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	334688
5°	304225
10°	224846
15°	139093
20°	79434
25°	45341
30°	25422
35°	13840
40°	7586
45°	4155
50°	2422
55°	1759
60°	1667
65°	1505
70°	1346
75°	1440
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4155 cd/sqm

TEST NUMBER: P1246831

CATALOG NUMBER: P3AS13R209024DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.7	27.5
10°-20°	170.9	39.3
20°-30°	89.2	20.5
30°-40°	34.5	7.9
40°-50°	11.2	2.6
50°-60°	4.4	1.0
60°-70°	2.9	0.7
70°-80°	1.7	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.7	87.3
0°-40°	414.2	95.2
0°-60°	429.8	98.8
0°-90°	435.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	435.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1526	
5°	1382	120
15°	613	171
25°	187	89
35°	52	34
45°	13	11
55°	5	4
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1246831

CATALOG NUMBER: P3AS13R209024DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1526.3
1°	1523.3
2°	1505.3
3°	1477.5
4°	1434.7
5°	1382.1
6°	1319.9
7°	1251.0
8°	1171.2
9°	1093.4
10°	1009.8
12.5°	802.6
15°	612.7
17.5°	458.5
20°	340.4
22.5°	252.1
25°	187.4
27.5°	138.3
30°	100.4
32.5°	72.7
35°	51.7
37.5°	37.4
40°	26.5
42.5°	18.9
45°	13.4
47.5°	9.7
50°	7.1
52.5°	5.5
55°	4.6
57.5°	4.2
60°	3.8
62.5°	3.4
65°	2.9
67.5°	2.5
70°	2.1
72.5°	2.1
75°	1.7
77.5°	1.3
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)