

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246841

Luminaire Tested: P3AS13R209024DE010 E3DLD1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1246841  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R209024DE010 E3DLD1WMH  
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 675.0 lumens  
Efficiency: N/A  
Efficacy: 46.2 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246841

CATALOG NUMBER: P3AS13R209024DE010 E3DLD1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1246841

CATALOG NUMBER: P3AS13R209024DE010 E3DLD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 109 | 106 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 96  |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  |  | 92  | 89  | 87  |  | 90  |
| 3   | 100 | 93  | 87  | 82  | 98  | 91  | 86  | 82  | 88  | 84  | 80  |  | 86  | 82  | 79  |  | 84  |
| 4   | 94  | 86  | 79  | 75  | 92  | 85  | 79  | 74  | 82  | 77  | 73  |  | 80  | 76  | 72  |  | 78  |
| 5   | 89  | 80  | 73  | 68  | 87  | 79  | 73  | 68  | 77  | 71  | 67  |  | 75  | 70  | 67  |  | 73  |
| 6   | 84  | 74  | 68  | 63  | 82  | 73  | 67  | 63  | 72  | 66  | 62  |  | 70  | 65  | 62  |  | 69  |
| 7   | 80  | 69  | 63  | 58  | 78  | 69  | 62  | 58  | 67  | 62  | 58  |  | 66  | 61  | 57  |  | 65  |
| 8   | 75  | 65  | 59  | 54  | 74  | 64  | 58  | 54  | 63  | 58  | 54  |  | 62  | 57  | 53  |  | 61  |
| 9   | 72  | 61  | 55  | 50  | 70  | 61  | 55  | 50  | 60  | 54  | 50  |  | 59  | 54  | 50  |  | 58  |
| 10  | 68  | 58  | 51  | 47  | 67  | 57  | 51  | 47  | 56  | 51  | 47  |  | 56  | 51  | 47  |  | 55  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 166960 |
| 5°  | 162513 |
| 10° | 149496 |
| 15° | 131579 |
| 20° | 112850 |
| 25° | 94796  |
| 30° | 76645  |
| 35° | 58303  |
| 40° | 41478  |
| 45° | 27383  |
| 50° | 16955  |
| 55° | 11163  |
| 60° | 10175  |
| 65° | 9340   |
| 70° | 8784   |
| 75° | 7964   |
| 80° | 7577   |
| 85° | 6542   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27383 cd/sqm

TEST NUMBER: P1246841

CATALOG NUMBER: P3AS13R209024DE010 E3DLD1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 68.3   | 10.1      |
| 10°-20°   | 161.4  | 23.9      |
| 20°-30°   | 179.1  | 26.5      |
| 30°-40°   | 136.6  | 20.2      |
| 40°-50°   | 70.0   | 10.4      |
| 50°-60°   | 28.8   | 4.3       |
| 60°-70°   | 17.9   | 2.7       |
| 70°-80°   | 10.0   | 1.5       |
| 80°-90°   | 2.9    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 408.8  | 60.6      |
| 0°-40°    | 545.4  | 80.8      |
| 0°-60°    | 644.1  | 95.4      |
| 0°-90°    | 675.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 675.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 761 |      |
| 5°  | 738 | 68   |
| 15° | 580 | 161  |
| 25° | 392 | 179  |
| 35° | 218 | 137  |
| 45° | 88  | 70   |
| 55° | 29  | 29   |
| 65° | 18  | 18   |
| 75° | 9   | 10   |
| 85° | 3   | 3    |
| 90° | 0   |      |

TEST NUMBER: P1246841

CATALOG NUMBER: P3AS13R209024DE010 E3DLD1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 761.4 |
| 1°    | 762.3 |
| 2°    | 758.8 |
| 3°    | 754.5 |
| 4°    | 747.7 |
| 5°    | 738.3 |
| 6°    | 727.1 |
| 7°    | 715.1 |
| 8°    | 702.2 |
| 9°    | 686.8 |
| 10°   | 671.4 |
| 12.5° | 626.8 |
| 15°   | 579.6 |
| 17.5° | 531.6 |
| 20°   | 483.6 |
| 22.5° | 435.6 |
| 25°   | 391.8 |
| 27.5° | 348.1 |
| 30°   | 302.7 |
| 32.5° | 259.8 |
| 35°   | 217.8 |
| 37.5° | 180.9 |
| 40°   | 144.9 |
| 42.5° | 114.0 |
| 45°   | 88.3  |
| 47.5° | 66.9  |
| 50°   | 49.7  |
| 52.5° | 36.9  |
| 55°   | 29.2  |
| 57.5° | 26.6  |
| 60°   | 23.2  |
| 62.5° | 20.6  |
| 65°   | 18.0  |
| 67.5° | 15.4  |
| 70°   | 13.7  |
| 72.5° | 11.1  |
| 75°   | 9.4   |
| 77.5° | 7.7   |
| 80°   | 6.0   |
| 82.5° | 4.3   |
| 85°   | 2.6   |
| 87.5° | 0.9   |
| 90°   | 0.0   |

(END OF REPORT)