

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248419

Luminaire Tested: P3AS05R209027DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248419
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209027DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 368.0 lumens
Efficiency: N/A
Efficacy: 51.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248419

CATALOG NUMBER: P3AS05R209027DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1248419

CATALOG NUMBER: P3AS05R209027DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91023
5°	88598
10°	81495
15°	71737
20°	61512
25°	51680
30°	41779
35°	31775
40°	22614
45°	14916
50°	9245
55°	6079
60°	5526
65°	5085
70°	4809
75°	4321
80°	4167
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14916 cd/sqm

TEST NUMBER: P1248419

CATALOG NUMBER: P3AS05R209027DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.2	10.1
10°-20°	88.0	23.9
20°-30°	97.6	26.5
30°-40°	74.5	20.2
40°-50°	38.1	10.4
50°-60°	15.7	4.3
60°-70°	9.8	2.7
70°-80°	5.5	1.5
80°-90°	1.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	222.8	60.6
0°-40°	297.3	80.8
0°-60°	351.1	95.4
0°-90°	368.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	368.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	415	
5°	402	37
15°	316	88
25°	214	98
35°	119	74
45°	48	38
55°	16	16
65°	10	10
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1248419

CATALOG NUMBER: P3AS05R209027DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	415.1
1°	415.6
2°	413.7
3°	411.4
4°	407.6
5°	402.5
6°	396.4
7°	389.9
8°	382.9
9°	374.4
10°	366.0
12.5°	341.7
15°	316.0
17.5°	289.8
20°	263.6
22.5°	237.5
25°	213.6
27.5°	189.8
30°	165.0
32.5°	141.6
35°	118.7
37.5°	98.6
40°	79.0
42.5°	62.2
45°	48.1
47.5°	36.5
50°	27.1
52.5°	20.1
55°	15.9
57.5°	14.5
60°	12.6
62.5°	11.2
65°	9.8
67.5°	8.4
70°	7.5
72.5°	6.1
75°	5.1
77.5°	4.2
80°	3.3
82.5°	2.3
85°	1.4
87.5°	0.5
90°	0.0

(END OF REPORT)