

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246869

Luminaire Tested: P3AS13R259024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246869
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 269.0 lumens
Efficiency: N/A
Efficacy: 18.4 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246869
CATALOG NUMBER: P3AS13R259024DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1246869
 CATALOG NUMBER: P3AS13R259024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97668
5°	93704
10°	82074
15°	65971
20°	50684
25°	38349
30°	27726
35°	18417
40°	11164
45°	6512
50°	4162
55°	3364
60°	2938
65°	2594
70°	2180
75°	2118
80°	1642
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6512 cd/sqm



TEST NUMBER: P1246869
 CATALOG NUMBER: P3AS13R259024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.7	14.4
10°-20°	80.4	29.9
20°-30°	72.7	27.0
30°-40°	43.7	16.2
40°-50°	17.3	6.4
50°-60°	8.0	3.0
60°-70°	4.9	1.8
70°-80°	2.6	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	191.8	71.3
0°-40°	235.4	87.5
0°-60°	260.8	97.0
0°-90°	269.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	269.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	445	
5°	426	39
15°	291	80
25°	158	73
35°	69	44
45°	21	17
55°	9	8
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1246869
CATALOG NUMBER: P3AS13R259024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	445.4
1°	445.4
2°	443.3
3°	438.7
4°	432.8
5°	425.7
6°	416.4
7°	406.0
8°	393.8
9°	381.6
10°	368.6
11°	353.5
12°	338.0
13°	322.5
14°	307.0
15°	290.6
17.5°	252.0
20°	217.2
22.5°	185.8
25°	158.5
27.5°	132.9
30°	109.5
32.5°	88.1
35°	68.8
37.5°	52.4
40°	39.0
42.5°	28.5
45°	21.0
47.5°	15.9
50°	12.2
52.5°	10.1
55°	8.8
57.5°	7.5
60°	6.7
62.5°	5.5
65°	5.0
67.5°	4.2
70°	3.4
72.5°	2.9
75°	2.5
77.5°	2.1
80°	1.3
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1246869
CATALOG NUMBER: P3AS13R259024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)