

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246929

Luminaire Tested: P3AS13R359024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 273.0 lumens
Efficiency: N/A
Efficacy: 18.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246929

CATALOG NUMBER: P3AS13R359024DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1246929

CATALOG NUMBER: P3AS13R359024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87756
5°	85582
10°	78244
15°	66425
20°	52575
25°	39776
30°	28941
35°	19568
40°	12023
45°	6915
50°	4162
55°	3364
60°	2938
65°	2594
70°	2180
75°	2118
80°	2147
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6915 cd/sqm

TEST NUMBER: P1246929

CATALOG NUMBER: P3AS13R359024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.9	13.2
10°-20°	80.7	29.5
20°-30°	75.5	27.6
30°-40°	46.2	16.9
40°-50°	18.2	6.7
50°-60°	8.0	2.9
60°-70°	5.0	1.8
70°-80°	2.7	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	192.0	70.3
0°-40°	238.2	87.3
0°-60°	264.4	96.9
0°-90°	273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	273.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	400	
5°	389	36
15°	293	81
25°	164	75
35°	73	46
45°	22	18
55°	9	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1246929

CATALOG NUMBER: P3AS13R359024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	400.2
1°	400.6
2°	399.3
3°	396.8
4°	393.0
5°	388.8
6°	383.4
7°	377.1
8°	369.5
9°	361.1
10°	351.4
11°	341.3
12°	330.4
13°	318.6
14°	305.6
15°	292.6
17.5°	258.9
20°	225.3
22.5°	192.9
25°	164.4
27.5°	137.9
30°	114.3
32.5°	92.5
35°	73.1
37.5°	55.9
40°	42.0
42.5°	30.3
45°	22.3
47.5°	16.0
50°	12.2
52.5°	10.1
55°	8.8
57.5°	7.6
60°	6.7
62.5°	5.9
65°	5.0
67.5°	4.2
70°	3.4
72.5°	2.9
75°	2.5
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4



TEST NUMBER: P1246929

CATALOG NUMBER: P3AS13R359024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)