

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246966

Luminaire Tested: P3AS13R409024DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246966
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409024DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 2400K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 630.0 lumens
Efficiency: N/A
Efficacy: 43.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246966

CATALOG NUMBER: P3AS13R409024DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246966

CATALOG NUMBER: P3AS13R409024DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	196168
5°	192207
10°	178955
15°	155960
20°	125684
25°	94215
30°	66238
35°	43393
40°	26278
45°	15692
50°	9347
55°	7531
60°	6754
65°	5811
70°	5514
75°	4321
80°	4293
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15692 cd/sqm

TEST NUMBER: P1246966

CATALOG NUMBER: P3AS13R409024DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.1	12.9
10°-20°	189.2	30.0
20°-30°	178.3	28.3
30°-40°	103.1	16.4
40°-50°	41.1	6.5
50°-60°	18.2	2.9
60°-70°	11.2	1.8
70°-80°	5.9	0.9
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	448.6	71.2
0°-40°	551.7	87.6
0°-60°	611.0	97.0
0°-90°	630.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	630.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	895	
5°	873	81
15°	687	189
25°	389	178
35°	162	103
45°	51	41
55°	20	18
65°	11	11
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1246966

CATALOG NUMBER: P3AS13R409024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	894.6
2.5°	889.4
5°	873.2
7.5°	843.1
10°	803.7
12.5°	750.5
15°	687.0
17.5°	615.8
20°	538.6
22.5°	461.4
25°	389.4
27.5°	322.5
30°	261.6
32.5°	208.4
35°	162.1
37.5°	122.7
40°	91.8
42.5°	68.6
45°	50.6
47.5°	36.9
50°	27.4
52.5°	22.3
55°	19.7
57.5°	18.0
60°	15.4
62.5°	12.9
65°	11.2
67.5°	9.4
70°	8.6
72.5°	6.9
75°	5.1
77.5°	4.3
80°	3.4
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)