

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246993

Luminaire Tested: P3AS13R509024DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246993
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509024DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1173.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246993

CATALOG NUMBER: P3AS13R509024DE010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1246993

CATALOG NUMBER: P3AS13R509024DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	101	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91	88	86	85
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87	84	82	80
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		83	80	77	76
6	92	84	79	75	91	83	79	75	82	78	74		81	77	74		79	76	73	72
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76	73	70	69
8	85	76	71	67	83	76	71	67	75	70	67		74	70	67		73	69	66	65
9	81	73	68	64	80	72	67	64	71	67	64		71	66	63		70	66	63	62
10	78	69	64	61	77	69	64	61	68	64	61		68	63	61		67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	408520
5°	401210
10°	385230
15°	353260
20°	311504
25°	238756
30°	129817
35°	41760
40°	9818
45°	1333
50°	1160
55°	1300
60°	1140
65°	1349
70°	1090
75°	1440
80°	1137
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 85°
Luminance: 2264 cd/sqm

TEST NUMBER: P1246993

CATALOG NUMBER: P3AS13R509024DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.0	14.6
10°-20°	432.6	36.9
20°-30°	433.2	36.9
30°-40°	121.8	10.4
40°-50°	7.4	0.6
50°-60°	2.8	0.2
60°-70°	2.2	0.2
70°-80°	1.5	0.1
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1036.8	88.4
0°-40°	1158.6	98.8
0°-60°	1168.7	99.6
0°-90°	1173.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1173.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1863	
5°	1823	171
15°	1556	433
25°	987	433
35°	156	122
45°	4	7
55°	3	3
65°	3	2
75°	2	1
85°	1	1
90°	0	

TEST NUMBER: P1246993

CATALOG NUMBER: P3AS13R509024DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1863.0
2.5°	1853.6
5°	1822.7
7.5°	1780.7
10°	1730.1
12.5°	1653.8
15°	1556.1
17.5°	1443.8
20°	1334.9
22.5°	1199.4
25°	986.8
27.5°	734.7
30°	512.7
32.5°	309.5
35°	156.0
37.5°	73.7
40°	34.3
42.5°	12.9
45°	4.3
47.5°	3.4
50°	3.4
52.5°	3.4
55°	3.4
57.5°	2.6
60°	2.6
62.5°	2.6
65°	2.6
67.5°	1.7
70°	1.7
72.5°	1.7
75°	1.7
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)