

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247003

Luminaire Tested: P3AS13R509024DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247003
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509024DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 473.0 lumens
Efficiency: N/A
Efficacy: 32.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247003

CATALOG NUMBER: P3AS13R509024DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1247003

CATALOG NUMBER: P3AS13R509024DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150602
5°	147567
10°	138207
15°	123724
20°	104122
25°	79480
30°	51654
35°	30624
40°	17690
45°	8869
50°	3309
55°	2561
60°	2412
65°	2179
70°	2180
75°	2118
80°	2147
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8869 cd/sqm

TEST NUMBER: P1247003

CATALOG NUMBER: P3AS13R509024DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.4	13.2
10°-20°	150.7	31.9
20°-30°	147.9	31.3
30°-40°	74.5	15.8
40°-50°	23.5	5.0
50°-60°	6.1	1.3
60°-70°	4.3	0.9
70°-80°	2.7	0.6
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	361.0	76.3
0°-40°	435.5	92.1
0°-60°	465.1	98.3
0°-90°	473.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	473.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	687	
5°	670	62
15°	545	151
25°	328	148
35°	114	74
45°	29	24
55°	7	6
65°	4	4
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1247003

CATALOG NUMBER: P3AS13R509024DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	686.8
2.5°	682.6
5°	670.4
7.5°	648.5
10°	620.7
12.5°	585.0
15°	545.0
17.5°	498.8
20°	446.2
22.5°	389.4
25°	328.5
27.5°	263.7
30°	204.0
32.5°	153.5
35°	114.4
37.5°	84.5
40°	61.8
42.5°	43.7
45°	28.6
47.5°	16.4
50°	9.7
52.5°	7.1
55°	6.7
57.5°	5.9
60°	5.5
62.5°	5.0
65°	4.2
67.5°	3.8
70°	3.4
72.5°	2.9
75°	2.5
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)