

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248546

Luminaire Tested: P3AS05R409027DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248546
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409027DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 545.0 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248546

CATALOG NUMBER: P3AS05R409027DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1248546

CATALOG NUMBER: P3AS05R409027DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	241165
5°	234162
10°	212488
15°	175552
20°	126618
25°	78319
30°	42412
35°	21924
40°	11908
45°	6667
50°	3343
55°	2485
60°	2237
65°	2179
70°	2116
75°	1949
80°	1768
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6667 cd/sqm

TEST NUMBER: P1248546

CATALOG NUMBER: P3AS05R409027DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	18.0
10°-20°	210.6	38.6
20°-30°	150.3	27.6
30°-40°	55.3	10.2
40°-50°	17.4	3.2
50°-60°	6.0	1.1
60°-70°	4.2	0.8
70°-80°	2.5	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	458.9	84.2
0°-40°	514.2	94.4
0°-60°	537.6	98.7
0°-90°	545.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	545.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1100	
5°	1064	98
15°	773	211
25°	324	150
35°	82	55
45°	22	17
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1248546

CATALOG NUMBER: P3AS05R409027DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1099.8
2.5°	1091.4
5°	1063.8
7.5°	1017.9
10°	954.3
12.5°	873.4
15°	773.3
17.5°	661.0
20°	542.6
22.5°	426.2
25°	323.7
27.5°	237.6
30°	167.5
32.5°	117.4
35°	81.9
37.5°	58.0
40°	41.6
42.5°	29.9
45°	21.5
47.5°	14.5
50°	9.8
52.5°	7.0
55°	6.5
57.5°	6.1
60°	5.1
62.5°	4.7
65°	4.2
67.5°	3.7
70°	3.3
72.5°	2.8
75°	2.3
77.5°	1.9
80°	1.4
82.5°	0.9
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)