

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247009

Luminaire Tested: P3AS13R509024DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509024DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 368.0 lumens
Efficiency: N/A
Efficacy: 25.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247009

CATALOG NUMBER: P3AS13R509024DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1247009

CATALOG NUMBER: P3AS13R509024DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		83
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		75
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		69
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		63
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		53
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		50
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74775
5°	73674
10°	70428
15°	65222
20°	58618
25°	51511
30°	43804
35°	35523
40°	26679
45°	17180
50°	8153
55°	6423
60°	6096
65°	5656
70°	5129
75°	4660
80°	4293
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17180 cd/sqm

TEST NUMBER: P1247009

CATALOG NUMBER: P3AS13R509024DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.4	8.5
10°-20°	80.1	21.8
20°-30°	97.3	26.4
30°-40°	82.5	22.4
40°-50°	42.9	11.6
50°-60°	15.5	4.2
60°-70°	10.7	2.9
70°-80°	5.8	1.6
80°-90°	1.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	208.8	56.7
0°-40°	291.3	79.2
0°-60°	349.6	95.0
0°-90°	368.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	368.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	341	
5°	335	31
15°	287	80
25°	213	97
35°	133	83
45°	55	43
55°	17	15
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1247009

CATALOG NUMBER: P3AS13R509024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	341.0
2.5°	339.8
5°	334.7
7.5°	327.2
10°	316.3
12.5°	302.4
15°	287.3
17.5°	270.1
20°	251.2
22.5°	231.8
25°	212.9
27.5°	193.2
30°	173.0
32.5°	152.9
35°	132.7
37.5°	113.0
40°	93.2
42.5°	74.3
45°	55.4
47.5°	37.0
50°	23.9
52.5°	18.5
55°	16.8
57.5°	15.1
60°	13.9
62.5°	12.2
65°	10.9
67.5°	9.2
70°	8.0
72.5°	6.7
75°	5.5
77.5°	4.2
80°	3.4
82.5°	2.5
85°	1.7
87.5°	0.8
90°	0.0

(END OF REPORT)