

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248567

Luminaire Tested: P3AS05R459027DE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1248567  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R459027DE010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 165.0 lumens  
Efficiency: N/A  
Efficacy: 22.9 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1248567  
CATALOG NUMBER: P3AS05R459027DE010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1248567  
 CATALOG NUMBER: P3AS05R459027DE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74				74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69				69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64				64
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60				60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56				56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	49141
5°	48030
10°	44310
15°	38525
20°	31643
25°	24630
30°	18180
35°	12796
40°	7986
45°	4342
50°	2354
55°	2026
60°	1798
65°	1557
70°	1346
75°	1356
80°	1137
85°	1258

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4342 cd/sqm



TEST NUMBER: P1248567  
 CATALOG NUMBER: P3AS05R459027DE010 E3DLP1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	20.2	12.2
10°-20°	46.9	28.4
20°-30°	46.6	28.2
30°-40°	30.0	18.2
40°-50°	11.6	7.0
50°-60°	4.7	2.9
60°-70°	3.0	1.8
70°-80°	1.6	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	113.7	68.9
0°-40°	143.7	87.1
0°-60°	159.9	96.9
0°-90°	165.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	165.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	224	
5°	218	20
15°	170	47
25°	102	47
35°	48	30
45°	14	12
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1248567  
CATALOG NUMBER: P3AS05R459027DE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	224.1
2.5°	223.0
5°	218.2
7.5°	209.9
10°	199.0
12.5°	185.2
15°	169.7
17.5°	152.8
20°	135.6
22.5°	118.2
25°	101.8
27.5°	86.2
30°	71.8
32.5°	59.2
35°	47.8
37.5°	37.5
40°	27.9
42.5°	20.1
45°	14.0
47.5°	9.4
50°	6.9
52.5°	5.7
55°	5.3
57.5°	4.6
60°	4.1
62.5°	3.4
65°	3.0
67.5°	2.5
70°	2.1
72.5°	1.8
75°	1.6
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)