

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247015

Luminaire Tested: P3AS13R509024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247015
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 310.0 lumens
Efficiency: N/A
Efficacy: 21.2 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247015

CATALOG NUMBER: P3AS13R509024DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1247015

CATALOG NUMBER: P3AS13R509024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90168
5°	87739
10°	80894
15°	71147
20°	59529
25°	47204
30°	34638
35°	23798
40°	15143
45°	8466
50°	4571
55°	3861
60°	3333
65°	3061
70°	2693
75°	2457
80°	2147
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8466 cd/sqm

TEST NUMBER: P1247015

CATALOG NUMBER: P3AS13R509024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.9	11.9
10°-20°	86.8	28.0
20°-30°	88.8	28.6
30°-40°	56.3	18.2
40°-50°	22.4	7.2
50°-60°	9.1	2.9
60°-70°	5.8	1.9
70°-80°	3.0	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	212.5	68.6
0°-40°	268.8	86.7
0°-60°	300.3	96.9
0°-90°	310.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	310.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	411	
5°	399	37
15°	313	87
25°	195	89
35°	89	56
45°	27	22
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1247015

CATALOG NUMBER: P3AS13R509024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	411.2
2.5°	408.2
5°	398.6
7.5°	383.5
10°	363.3
12.5°	339.4
15°	313.4
17.5°	284.9
20°	255.1
22.5°	225.3
25°	195.1
27.5°	164.9
30°	136.8
32.5°	111.6
35°	88.9
37.5°	69.6
40°	52.9
42.5°	39.0
45°	27.3
47.5°	18.5
50°	13.4
52.5°	11.3
55°	10.1
57.5°	8.8
60°	7.6
62.5°	6.7
65°	5.9
67.5°	5.0
70°	4.2
72.5°	3.4
75°	2.9
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)