

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248572

Luminaire Tested: P3AS05R459027DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248572
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459027DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 337.0 lumens
Efficiency: N/A
Efficacy: 46.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248572

CATALOG NUMBER: P3AS05R459027DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1248572

CATALOG NUMBER: P3AS05R459027DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100387
5°	98085
10°	90490
15°	78684
20°	64639
25°	50301
30°	37145
35°	26127
40°	16316
45°	8838
50°	4776
55°	4091
60°	3684
65°	3165
70°	2693
75°	2796
80°	2399
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8838 cd/sqm

TEST NUMBER: P1248572

CATALOG NUMBER: P3AS05R459027DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.3	12.2
10°-20°	95.8	28.4
20°-30°	95.1	28.2
30°-40°	61.3	18.2
40°-50°	23.6	7.0
50°-60°	9.6	2.8
60°-70°	6.1	1.8
70°-80°	3.3	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	232.2	68.9
0°-40°	293.5	87.1
0°-60°	326.7	96.9
0°-90°	337.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	337.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	458	
5°	446	41
15°	347	96
25°	208	95
35°	98	61
45°	28	24
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1248572

CATALOG NUMBER: P3AS05R459027DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	457.8
2.5°	455.4
5°	445.6
7.5°	428.8
10°	406.4
12.5°	378.4
15°	346.6
17.5°	312.0
20°	277.0
22.5°	241.5
25°	207.9
27.5°	176.1
30°	146.7
32.5°	121.0
35°	97.6
37.5°	76.6
40°	57.0
42.5°	41.1
45°	28.5
47.5°	19.2
50°	14.0
52.5°	11.7
55°	10.7
57.5°	9.3
60°	8.4
62.5°	7.0
65°	6.1
67.5°	5.1
70°	4.2
72.5°	3.7
75°	3.3
77.5°	2.3
80°	1.9
82.5°	1.4
85°	0.9
87.5°	0.5
90°	0.0

(END OF REPORT)