

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247019

Luminaire Tested: P3AS13R509024DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247019
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509024DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 964.0 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247019
CATALOG NUMBER: P3AS13R509024DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1247019
 CATALOG NUMBER: P3AS13R509024DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82				82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76				76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67				67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64				64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60				60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57				57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54				54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	306927
5°	300726
10°	281692
15°	252169
20°	212212
25°	161961
30°	105257
35°	62399
40°	36068
45°	18079
50°	6720
55°	5238
60°	4868
65°	4462
70°	4424
75°	4321
80°	4293
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18079 cd/sqm



TEST NUMBER: P1247019
 CATALOG NUMBER: P3AS13R509024DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.1	13.2
10°-20°	307.2	31.9
20°-30°	301.4	31.3
30°-40°	151.8	15.7
40°-50°	48.0	5.0
50°-60°	12.4	1.3
60°-70°	8.8	0.9
70°-80°	5.4	0.6
80°-90°	1.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	735.7	76.3
0°-40°	887.5	92.1
0°-60°	947.9	98.3
0°-90°	964.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	964.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1400	
5°	1366	127
15°	1111	307
25°	669	301
35°	233	152
45°	58	48
55°	14	12
65°	9	9
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1247019
CATALOG NUMBER: P3AS13R509024DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1399.7
2.5°	1391.1
5°	1366.2
7.5°	1321.7
10°	1265.1
12.5°	1192.2
15°	1110.8
17.5°	1016.5
20°	909.4
22.5°	793.7
25°	669.4
27.5°	537.4
30°	415.7
32.5°	312.8
35°	233.1
37.5°	172.3
40°	126.0
42.5°	89.1
45°	58.3
47.5°	33.4
50°	19.7
52.5°	14.6
55°	13.7
57.5°	12.0
60°	11.1
62.5°	10.3
65°	8.6
67.5°	7.7
70°	6.9
72.5°	6.0
75°	5.1
77.5°	4.3
80°	3.4
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)