

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248579

Luminaire Tested: P3AS05R509027DE010 E3D1H

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1248579  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R509027DE010 E3D1H  
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 649.0 lumens  
Efficiency: N/A  
Efficacy: 90.1 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1248579  
CATALOG NUMBER: P3AS05R509027DE010 E3D1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1248579  
 CATALOG NUMBER: P3AS05R509027DE010 E3D1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95				95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90				90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85				85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80				80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76				76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72				72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	68				68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	65				65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62				62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	59				59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	226802
5°	220757
10°	210662
15°	190716
20°	165004
25°	135347
30°	77759
35°	24146
40°	6498
45°	2264
50°	546
55°	191
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2264 cd/sqm



TEST NUMBER: P1248579  
 CATALOG NUMBER: P3AS05R509027DE010 E3D1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.9	14.5
10°-20°	232.8	35.9
20°-30°	244.7	37.7
30°-40°	70.0	10.8
40°-50°	6.8	1.1
50°-60°	0.6	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	571.4	88.0
0°-40°	641.4	98.8
0°-60°	648.8	100.0
0°-90°	649.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	649.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1034	
5°	1003	94
15°	840	233
25°	559	245
35°	90	70
45°	7	7
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1248579  
CATALOG NUMBER: P3AS05R509027DE010 E3D1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1034.3
1°	1032.7
2°	1028.1
3°	1021.5
4°	1012.5
5°	1002.9
6°	992.6
7°	981.6
8°	971.3
9°	959.4
10°	946.1
11°	930.8
12°	913.2
13°	891.2
14°	867.4
15°	840.1
16°	811.3
17°	783.3
18°	754.7
19°	729.5
20°	707.1
21°	685.6
22°	661.1
23°	632.9
24°	599.9
25°	559.4
26°	515.4
27°	466.4
28°	417.7
29°	365.0
30°	307.1
31°	252.8
32°	202.9
32.5°	181.1
33°	159.1
34°	122.0
35°	90.2
36°	66.2
37°	49.2
37.5°	42.6
38°	36.9
39°	28.6
40°	22.7
42.5°	12.8
45°	7.3



TEST NUMBER: P1248579  
CATALOG NUMBER: P3AS05R509027DE010 E3D1H

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	4.1
50°	1.6
52.5°	0.7
55°	0.5
57.5°	0.5
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)