

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248584

Luminaire Tested: P3AS05R509027DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248584
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509027DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 258.0 lumens
Efficiency: N/A
Efficacy: 35.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248584

CATALOG NUMBER: P3AS05R509027DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1248584

CATALOG NUMBER: P3AS05R509027DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82143
5°	80497
10°	75394
15°	67492
20°	56798
25°	43357
30°	28182
35°	16704
40°	9647
45°	4838
50°	1808
55°	1415
60°	1316
65°	1193
70°	1154
75°	1186
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4838 cd/sqm

TEST NUMBER: P1248584

CATALOG NUMBER: P3AS05R509027DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.0	13.2
10°-20°	82.2	31.9
20°-30°	80.7	31.3
30°-40°	40.6	15.7
40°-50°	12.8	5.0
50°-60°	3.3	1.3
60°-70°	2.4	0.9
70°-80°	1.4	0.6
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.9	76.3
0°-40°	237.5	92.1
0°-60°	253.7	98.3
0°-90°	258.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	258.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	375	
5°	366	34
15°	297	82
25°	179	81
35°	62	41
45°	16	13
55°	4	3
65°	2	2
75°	1	1
85°	0	1
90°	0	

TEST NUMBER: P1248584

CATALOG NUMBER: P3AS05R509027DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	374.6
2.5°	372.3
5°	365.7
7.5°	353.7
10°	338.6
12.5°	319.1
15°	297.3
17.5°	272.1
20°	243.4
22.5°	212.4
25°	179.2
27.5°	143.8
30°	111.3
32.5°	83.7
35°	62.4
37.5°	46.1
40°	33.7
42.5°	23.9
45°	15.6
47.5°	8.9
50°	5.3
52.5°	3.9
55°	3.7
57.5°	3.2
60°	3.0
62.5°	2.8
65°	2.3
67.5°	2.1
70°	1.8
72.5°	1.6
75°	1.4
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)