

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248618

Luminaire Tested: P3AS05R559027DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248618
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559027DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 509.0 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248618

CATALOG NUMBER: P3AS05R559027DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1248618

CATALOG NUMBER: P3AS05R559027DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139770
5°	138344
10°	133598
15°	123497
20°	106573
25°	84174
30°	59705
35°	38494
40°	23129
45°	13025
50°	6993
55°	2485
60°	2237
65°	2179
70°	2116
75°	1949
80°	1768
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13025 cd/sqm

TEST NUMBER: P1248618

CATALOG NUMBER: P3AS05R559027DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.1	11.6
10°-20°	150.4	29.6
20°-30°	157.6	31.0
30°-40°	92.0	18.1
40°-50°	34.4	6.8
50°-60°	8.1	1.6
60°-70°	4.2	0.8
70°-80°	2.5	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	367.2	72.1
0°-40°	459.2	90.2
0°-60°	501.7	98.6
0°-90°	509.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	509.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	637	
5°	628	59
15°	544	150
25°	348	158
35°	144	92
45°	42	34
55°	6	8
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1248618

CATALOG NUMBER: P3AS05R559027DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	637.4
2.5°	635.5
5°	628.5
7.5°	617.3
10°	600.0
12.5°	575.8
15°	544.0
17.5°	503.8
20°	456.7
22.5°	403.9
25°	347.9
27.5°	290.4
30°	235.8
32.5°	186.3
35°	143.8
37.5°	109.3
40°	80.8
42.5°	57.9
45°	42.0
47.5°	30.4
50°	20.5
52.5°	11.7
55°	6.5
57.5°	5.6
60°	5.1
62.5°	4.7
65°	4.2
67.5°	3.7
70°	3.3
72.5°	2.8
75°	2.3
77.5°	1.9
80°	1.4
82.5°	0.9
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)