

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247057

Luminaire Tested: P3AS13R609024DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247057
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609024DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1027.0 lumens
Efficiency: N/A
Efficacy: 70.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247057
CATALOG NUMBER: P3AS13R609024DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1247057

CATALOG NUMBER: P3AS13R609024DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82			82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77			77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72			72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67			67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63			63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59			59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56			56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53			53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	269079
5°	254017
10°	247424
15°	241772
20°	224790
25°	200963
30°	153492
35°	88606
40°	34407
45°	14327
50°	3138
55°	497
60°	351
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14327 cd/sqm



TEST NUMBER: P1247057
 CATALOG NUMBER: P3AS13R609024DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.9	10.6
10°-20°	296.7	28.9
20°-30°	371.6	36.2
30°-40°	207.7	20.2
40°-50°	39.5	3.8
50°-60°	2.0	0.2
60°-70°	0.4	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	777.2	75.7
0°-40°	984.9	95.9
0°-60°	1026.4	99.9
0°-90°	1027.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1027.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1227	
5°	1154	109
15°	1065	297
25°	831	372
35°	331	208
45°	46	39
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1247057

CATALOG NUMBER: P3AS13R609024DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1227.1
1°	1222.1
2°	1206.1
3°	1187.2
4°	1169.6
5°	1154.0
6°	1142.3
7°	1132.2
8°	1124.6
9°	1117.5
10°	1111.2
11°	1104.9
12°	1097.7
13°	1088.9
14°	1078.4
15°	1065.0
16°	1048.6
17°	1030.1
18°	1009.1
19°	985.2
20°	963.3
21°	939.8
22°	915.4
23°	889.8
24°	861.6
25°	830.6
26°	794.0
27°	753.3
28°	707.5
29°	658.7
30°	606.2
31°	553.3
32°	498.7
32.5°	468.8
33°	442.0
34°	386.1
35°	331.0
36°	281.5
37°	229.0
37.5°	205.0
38°	181.5
39°	146.2
40°	120.2
42.5°	73.1
45°	46.2



TEST NUMBER: P1247057
CATALOG NUMBER: P3AS13R609024DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	25.6
50°	9.2
52.5°	2.1
55°	1.3
57.5°	0.8
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)