

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248642

Luminaire Tested: P3AS05R609027DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248642
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609027DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 241.0 lumens
Efficiency: N/A
Efficacy: 33.5 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248642

CATALOG NUMBER: P3AS05R609027DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1248642

CATALOG NUMBER: P3AS05R609027DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56903
5°	56372
10°	54731
15°	51260
20°	45387
25°	37962
30°	29751
35°	21576
40°	14370
45°	8962
50°	4844
55°	1415
60°	1316
65°	1193
70°	1154
75°	1186
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8962 cd/sqm

TEST NUMBER: P1248642

CATALOG NUMBER: P3AS05R609027DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.1	10.0
10°-20°	62.7	26.0
20°-30°	71.4	29.6
30°-40°	50.6	21.0
40°-50°	23.0	9.5
50°-60°	4.9	2.0
60°-70°	2.3	1.0
70°-80°	1.4	0.6
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	158.2	65.6
0°-40°	208.8	86.7
0°-60°	236.7	98.2
0°-90°	241.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	241.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	260	
5°	256	24
15°	226	63
25°	157	71
35°	81	51
45°	29	23
55°	4	5
65°	2	2
75°	1	1
85°	0	1
90°	0	

TEST NUMBER: P1248642

CATALOG NUMBER: P3AS05R609027DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	259.5
2.5°	258.6
5°	256.1
7.5°	251.7
10°	245.8
12.5°	237.3
15°	225.8
17.5°	211.4
20°	194.5
22.5°	176.1
25°	156.9
27.5°	137.2
30°	117.5
32.5°	98.7
35°	80.6
37.5°	64.6
40°	50.2
42.5°	38.0
45°	28.9
47.5°	21.5
50°	14.2
52.5°	6.6
55°	3.7
57.5°	3.2
60°	3.0
62.5°	2.7
65°	2.3
67.5°	2.1
70°	1.8
72.5°	1.6
75°	1.4
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)