

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247079

Luminaire Tested: P3AS13R659024DE010 E3CB1MB

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1247079  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R659024DE010 E3CB1MB  
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3CB1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1060.0 lumens  
Efficiency: N/A  
Efficacy: 72.6 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247079  
CATALOG NUMBER: P3AS13R659024DE010 E3CB1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1247079  
 CATALOG NUMBER: P3AS13R659024DE010 E3CB1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	259036
5°	243803
10°	240699
15°	236460
20°	223249
25°	207206
30°	161063
35°	93184
40°	37556
45°	17273
50°	6720
55°	2638
60°	2237
65°	2231
70°	2180
75°	2203
80°	2147
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17273 cd/sqm



TEST NUMBER: P1247079  
 CATALOG NUMBER: P3AS13R659024DE010 E3CB1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.3	9.9
10°-20°	290.9	27.4
20°-30°	380.8	35.9
30°-40°	220.5	20.8
40°-50°	47.2	4.5
50°-60°	7.7	0.7
60°-70°	4.2	0.4
70°-80°	2.5	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	776.9	73.3
0°-40°	997.5	94.1
0°-60°	1052.3	99.3
0°-90°	1060.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1060.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1181	
5°	1108	105
15°	1042	291
25°	856	381
35°	348	221
45°	56	47
55°	7	8
65°	4	4
75°	3	2
85°	1	1
90°	0	



TEST NUMBER: P1247079  
CATALOG NUMBER: P3AS13R659024DE010 E3CB1MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1181.3
2.5°	1147.9
5°	1107.6
7.5°	1091.3
10°	1081.0
12.5°	1066.4
15°	1041.6
17.5°	1003.0
20°	956.7
22.5°	913.0
25°	856.4
27.5°	761.3
30°	636.1
32.5°	492.9
35°	348.1
37.5°	220.3
40°	131.2
42.5°	82.3
45°	55.7
47.5°	36.0
50°	19.7
52.5°	9.4
55°	6.9
57.5°	6.0
60°	5.1
62.5°	5.1
65°	4.3
67.5°	3.4
70°	3.4
72.5°	2.6
75°	2.6
77.5°	1.7
80°	1.7
82.5°	0.9
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)