

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247121

Luminaire Tested: P3AS13R709024DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247121
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709024DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 863.0 lumens
Efficiency: N/A
Efficacy: 59.1 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247121

CATALOG NUMBER: P3AS13R709024DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1247121

CATALOG NUMBER: P3AS13R709024DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	96	93		104	99	95	92		96	92	90		93	90	88		90	88	86
3	100	93	88	83		98	92	87	82		89	85	81		86	83	80		84	81	79
4	94	86	80	75		93	85	79	75		83	78	74		81	76	73		79	75	72
5	89	80	73	69		87	79	73	68		77	72	68		75	71	67		74	70	66
6	84	74	68	63		82	73	67	63		72	66	62		70	65	62		69	65	61
7	79	69	62	58		78	68	62	58		67	61	57		66	61	57		65	60	57
8	75	65	58	53		74	64	58	53		63	57	53		62	57	53		61	56	53
9	71	60	54	50		70	60	54	50		59	53	49		58	53	49		57	52	49
10	67	57	50	46		66	56	50	46		55	50	46		55	49	46		54	49	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	167070
5°	165067
10°	160295
15°	153508
20°	143793
25°	130629
30°	112853
35°	89945
40°	65494
45°	43043
50°	20161
55°	6232
60°	6008
65°	5759
70°	5514
75°	5846
80°	5430
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 43043 cd/sqm

TEST NUMBER: P1247121

CATALOG NUMBER: P3AS13R709024DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.6	8.2
10°-20°	189.2	21.9
20°-30°	246.0	28.5
30°-40°	208.7	24.2
40°-50°	107.6	12.5
50°-60°	20.7	2.4
60°-70°	11.2	1.3
70°-80°	6.9	0.8
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	505.8	58.6
0°-40°	714.5	82.8
0°-60°	842.9	97.7
0°-90°	863.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	863.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	762	
5°	750	71
15°	676	189
25°	540	246
35°	336	209
45°	139	108
55°	16	21
65°	11	11
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1247121

CATALOG NUMBER: P3AS13R709024DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	761.9
2.5°	759.3
5°	749.9
7.5°	736.2
10°	719.9
12.5°	699.3
15°	676.2
17.5°	647.9
20°	616.2
22.5°	580.2
25°	539.9
27.5°	494.5
30°	445.7
32.5°	391.7
35°	336.0
37.5°	281.1
40°	228.8
42.5°	180.0
45°	138.8
47.5°	102.0
50°	59.1
52.5°	25.7
55°	16.3
57.5°	15.4
60°	13.7
62.5°	12.9
65°	11.1
67.5°	10.3
70°	8.6
72.5°	7.7
75°	6.9
77.5°	5.1
80°	4.3
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)