

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248690

Luminaire Tested: P3AS05R709027DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248690
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709027DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 585.0 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248690

CATALOG NUMBER: P3AS05R709027DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1248690

CATALOG NUMBER: P3AS05R709027DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116175
5°	110852
10°	105453
15°	102634
20°	98849
25°	93562
30°	87026
35°	73107
40°	47117
45°	21894
50°	5731
55°	1415
60°	1447
65°	1193
70°	1218
75°	1186
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21894 cd/sqm

TEST NUMBER: P1248690

CATALOG NUMBER: P3AS05R709027DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.1	8.1
10°-20°	127.0	21.7
20°-30°	177.5	30.3
30°-40°	164.6	28.1
40°-50°	59.0	10.1
50°-60°	5.0	0.9
60°-70°	2.5	0.4
70°-80°	1.6	0.3
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	351.7	60.1
0°-40°	516.3	88.3
0°-60°	580.3	99.2
0°-90°	585.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	585.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	530	
5°	504	47
15°	452	127
25°	387	177
35°	273	165
45°	71	59
55°	4	5
65°	2	2
75°	1	2
85°	0	1
90°	0	

TEST NUMBER: P1248690

CATALOG NUMBER: P3AS05R709027DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	529.8
2.5°	521.8
5°	503.6
7.5°	486.7
10°	473.6
12.5°	462.9
15°	452.1
17.5°	439.0
20°	423.6
22.5°	405.8
25°	386.7
27.5°	367.0
30°	343.7
32.5°	313.7
35°	273.1
37.5°	221.2
40°	164.6
42.5°	112.2
45°	70.6
47.5°	39.3
50°	16.8
52.5°	5.6
55°	3.7
57.5°	3.3
60°	3.3
62.5°	2.8
65°	2.3
67.5°	2.3
70°	1.9
72.5°	1.9
75°	1.4
77.5°	1.4
80°	0.9
82.5°	0.9
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)