

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248743

Luminaire Tested: P3AS09R109027DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248743
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R109027DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R10 optic, 2700K CCT AND, 90CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 425.1 lumens
Efficiency: N/A
Efficacy: 34.0 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248743

CATALOG NUMBER: P3AS09R109027DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1248743

CATALOG NUMBER: P3AS09R109027DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	98	90	83	79	96	88	83	78	85	81	77		83	79	75		81
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	70	63	58	79	70	63	58	68	62	58		67	61	57		65
7	77	66	59	54	75	65	58	54	64	58	53		62	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	69	58	51	46	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123674
5°	115936
10°	95077
15°	73871
20°	58292
25°	46454
30°	37297
35°	30437
40°	25076
45°	21118
50°	18115
55°	15674
60°	13902
65°	12089
70°	10771
75°	8727
80°	7072
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21118 cd/sqm

TEST NUMBER: P1248743

CATALOG NUMBER: P3AS09R109027DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	11.1
10°-20°	91.1	21.4
20°-30°	88.6	20.8
30°-40°	71.6	16.8
40°-50°	53.2	12.5
50°-60°	37.1	8.7
60°-70°	23.3	5.5
70°-80°	11.1	2.6
80°-90°	2.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	226.8	53.3
0°-40°	298.4	70.2
0°-60°	388.7	91.4
0°-90°	425.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	425.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	564	
5°	527	47
15°	325	91
25°	192	89
35°	114	72
45°	68	53
55°	41	37
65°	23	23
75°	10	11
85°	2	2
90°	0	

TEST NUMBER: P1248743

CATALOG NUMBER: P3AS09R109027DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	564.0
2.5°	554.7
5°	526.7
7.5°	482.0
10°	427.0
12.5°	372.9
15°	325.4
17.5°	285.3
20°	249.8
22.5°	219.1
25°	192.0
27.5°	167.8
30°	147.3
32.5°	129.6
35°	113.7
37.5°	99.8
40°	87.6
42.5°	77.4
45°	68.1
47.5°	60.6
50°	53.1
52.5°	46.6
55°	41.0
57.5°	36.4
60°	31.7
62.5°	27.0
65°	23.3
67.5°	19.6
70°	16.8
72.5°	13.1
75°	10.3
77.5°	7.5
80°	5.6
82.5°	2.8
85°	1.9
87.5°	0.0
90°	0.0

(END OF REPORT)