

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248757

Luminaire Tested: P3AS09R159027DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248757
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159027DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 709.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248757
CATALOG NUMBER: P3AS09R159027DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1248757
 CATALOG NUMBER: P3AS09R159027DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	605675
5°	537617
10°	373362
15°	220796
20°	125754
25°	71883
30°	39778
35°	21201
40°	11736
45°	6357
50°	3957
55°	3135
60°	2675
65°	2491
70°	2180
75°	2288
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6357 cd/sqm



TEST NUMBER: P1248757
 CATALOG NUMBER: P3AS09R159027DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.7	29.3
10°-20°	274.1	38.7
20°-30°	141.1	19.9
30°-40°	53.0	7.5
40°-50°	17.3	2.4
50°-60°	7.5	1.1
60°-70°	4.7	0.7
70°-80°	2.8	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.9	87.9
0°-40°	675.9	95.3
0°-60°	700.7	98.8
0°-90°	709.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	709.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2762	
5°	2442	208
15°	973	274
25°	297	141
35°	79	53
45°	20	17
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1248757
CATALOG NUMBER: P3AS09R159027DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2762.1
1°	2756.6
2°	2720.4
3°	2651.4
4°	2560.6
5°	2442.4
6°	2308.6
7°	2161.7
8°	1998.5
9°	1837.3
10°	1676.8
12.5°	1290.2
15°	972.6
17.5°	728.1
20°	538.9
22.5°	402.3
25°	297.1
27.5°	216.5
30°	157.1
32.5°	111.3
35°	79.2
37.5°	56.7
40°	41.0
42.5°	29.4
45°	20.5
47.5°	15.0
50°	11.6
52.5°	9.6
55°	8.2
57.5°	6.8
60°	6.1
62.5°	5.5
65°	4.8
67.5°	4.1
70°	3.4
72.5°	3.4
75°	2.7
77.5°	2.0
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)