

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1248773

Luminaire Tested: P3AS09R159027DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1248773
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159027DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 421.0 lumens
Efficiency: N/A
Efficacy: 37.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1248773

CATALOG NUMBER: P3AS09R159027DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1248773

CATALOG NUMBER: P3AS09R159027DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181542
5°	167796
10°	133954
15°	101181
20°	77053
25°	58721
30°	42057
35°	27438
40°	16832
45°	10172
50°	6755
55°	5238
60°	4517
65°	3891
70°	3526
75°	3474
80°	2652
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10172 cd/sqm

TEST NUMBER: P1248773

CATALOG NUMBER: P3AS09R159027DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.5	16.0
10°-20°	124.6	29.6
20°-30°	110.9	26.3
30°-40°	65.6	15.6
40°-50°	26.9	6.4
50°-60°	12.6	3.0
60°-70°	7.7	1.8
70°-80°	4.1	1.0
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	303.0	72.0
0°-40°	368.6	87.6
0°-60°	408.2	97.0
0°-90°	421.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	421.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	828	
5°	762	68
15°	446	125
25°	243	111
35°	102	66
45°	33	27
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1248773

CATALOG NUMBER: P3AS09R159027DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	827.9
1°	825.9
2°	819.7
3°	807.4
4°	786.9
5°	762.3
6°	735.6
7°	704.2
8°	671.4
9°	637.9
10°	601.6
12.5°	518.9
15°	445.7
17.5°	382.8
20°	330.2
22.5°	283.7
25°	242.7
27.5°	203.0
30°	166.1
32.5°	132.6
35°	102.5
37.5°	78.6
40°	58.8
42.5°	43.8
45°	32.8
47.5°	25.3
50°	19.8
52.5°	16.4
55°	13.7
57.5°	11.6
60°	10.3
62.5°	8.9
65°	7.5
67.5°	6.8
70°	5.5
72.5°	4.8
75°	4.1
77.5°	2.7
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)